

RSF64EXS & RSF64EXT

Variable insertion depth Float Switches

A vertical float switch, with either normally open or normally closed (when the float is down) switching action, permanently coupled to a 300mm PVC tube. This provides a float switch, whose overall depth can be varied between 150mm and 450mm, by adjusting its position in a sliding clamp.

Further 306mm PVC extension tubes may be added, up to a maximum of three, to provide insertion depths up to 1350mm.

TECHNICAL SPECIFICATIONS

Operating Temperature	°C	0 / +75
Minimum S.G. of Fluid		0.80
Float material		Polypropylene
Stem material		Polyphenylene Sulphide
Tube material		PVC Class 7
Cable length	Metres	1.5
Maximum Switching Voltage	V ac/dc	50
Maximum Switching Current	A	0.5
Maximum Switching Power	W/VA	10
Electrical life	Ops	5 x 10 ⁶

Farnell stock no.	730-683	730-695
Crydom Pt no.	RSF64EXS	RSF64EXT
Switching		
Action	N/O	Tube only
Switching depth	123 - 423mm	Add 306mm per


Other configurations can be configured, by Crydom, using combinations of any of the RSF60 series float switches and a PVC extension tube. Contact Crydom Sales for advice on particular requirements.

Every effort has been made to ensure that the descriptions and specifications quoted are correct, however, no liability can be accepted for any errors or omissions in this data. The detail specifications are subject to change without prior notice.


RSF64-2000Farnell

CRYDOM


Control over power



Switch Assembly



Extension Assembly



- **Insertion Depth**
150mm - 1350mm
- **Easy to install**
- **Adjustable Level**

Crydom Magnetics Ltd
7 Cobham Road
Ferndown Industrial Estate
Wimborne
Dorset BH21 7PE
Tel: +44 (0) 1202 897969
Fax: +44 (0) 1202 891918
magnetics@crydom.com
www.crydom.co.uk