


- 1 AMP TRADEMARK AND MOLD CAVITY IDENTIFICATION LOCATED AT EITHER END OF THE HOUSING IN APPROXIMATE LOCATION SHOWN.
- 2 THIS HOLE IS FOR MOLDING PURPOSES ONLY AND MAY BE FLASHED OVER.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.
- 4 WINDOWS MAY OR MAY NOT BE PRESENT ON THIS END OF THE HOUSING.



	OBSOLETE	2.594	2.500	25	26	2-487378-6
		3.394	3.300	33	34	2-487378-5
3	OBSOLETE	2.494	2.400	24	25	2-487378-4
		2.394	2.300	23	24	2-487378-3
3	OBSOLETE	2.294	2.200	22	23	2-487378-2
		2.194	2.100	21	22	2-487378-1
		2.094	2.000	20	21	2-487378-0
		1.994	1.900	19	20	1-487378-9
		1.894	1.800	18	19	1-487378-8
		1.794	1.700	17	18	1-487378-7
		1.694	1.600	16	17	1-487378-6
		1.594	1.500	15	16	1-487378-5
		1.494	1.400	14	15	1-487378-4
		1.394	1.300	13	14	1-487378-3
		1.294	1.200	12	13	1-487378-2
		1.194	1.100	11	12	1-487378-1
		1.094	1.000	10	11	1-487378-0
		.994	.900	9	10	487378-9
		.894	.800	8	9	487378-8
		.794	.700	7	8	487378-7
		.694	.600	6	7	487378-6
		.594	.500	5	6	487378-5
		.494	.400	4	5	487378-4
		.394	.300	3	4	487378-3
		.294	.200	2	3	487378-2
		.194	.100	1	2	487378-1
	C REF	B	A	NO OF POSNS	PRODUCT PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN D. DOLLYHIGH CHK D.R. WORTHINGTON		10-17-84 10-17-84				TE Connectivity								
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD —		NAME											
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± ± —		PRODUCT SPEC		HOUSING, RECEPTACLE, FFC											
				108-9024		—											
				APPLICATION SPEC		—											
				114-16015		—											
MATERIAL THERMOPLASTIC,		FINISH		WEIGHT		SIZE A2		CAGE CODE 00779		DRAWING NO C-487378		RESTRICTED TO —					
				CUSTOMER DRAWING								SCALE NTS		SHEET 1 of 1		REV V	