

Broadband Solutions

CX3899974 | 300G135 EMPTY DUCT COEX

ConQuest® Empty Conduit, 3 in, SDR 13.5, gray

Dimensions

Nominal Size	3 in
Wall Thickness Designation	SDR 13.5
Inner Diameter, nominal	74.981 mm 2.952 in
Length	304.80 m 1000.00 ft
Outer Diameter, nominal	88.900 mm 3.500 in
Wall Thickness, minimum	6.579 mm 0.259 in
Weight	1154.0 lb/kft

General Specifications

Color	Gray
Conduit Type	Non-toneable
Wall Type	Smooth
Brand	ConQuest®
Warranty	One year

Material Specifications

Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³
Density, minimum	0.941 g/cm ³
Design Standard	ASTM D3350-05
Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B
Flexural Modulus, minimum	552 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	21 N/mm ² 3000 psi

Mechanical Specifications

Minimum Bend Radius, unsupported	1219.2 mm 48.0 in
----------------------------------	---------------------

CX3899974 | 300G135 EMPTY DUCT COEX

Pulling Tension, maximum 2535.6 kg | 5590.0 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance