


High Stability Thin Film Flat Chip Resistors



Vishay Automotive Grade TNPW e3 thin film flat chip resistors are the perfect choice for most fields of modern electronics where highest reliability and stability is of major concern. Typical applications include automotive, industrial, test and measuring equipment, and medical equipment.

FEATURES

- Rated dissipation P_{70} up to 0.52 W for size 1206
- AEC-Q200 qualified
- Single lot date code (optional)
- Permissible film temperature up to 175 °C
- Superior temperature cycling robustness
- Excellent overall stability at different environmental conditions
- Superior moisture resistivity, $|\Delta R/R| < 0.1 \%$ (85 °C; 85 % RH; 1000 h)
- Superior sulfur resistance verified according to ASTM B 809 and ANSI/EIA-977
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE
GRADE

RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- Automotive
- Industrial equipment with enhanced requirements
- Test and measuring equipment
- Medical equipment

TECHNICAL SPECIFICATIONS

DESCRIPTION	TNPW0201 e3	TNPW0402 e3	TNPW0603 e3	TNPW0805 e3	TNPW1206 e3	TNPW1210 e3
Imperial size	0201	0402	0603	0805	1206	1210
Metric size code	RR0603M	RR1005M	RR1608M	RR2012M	RR3216M	RR3225M
Resistance range	22 Ω to 40 kΩ	10 Ω to 100 kΩ	1 Ω to 332 kΩ	1 Ω to 1 MΩ	1 Ω to 2 MΩ	10 Ω to 3.01 MΩ
Resistance tolerance	± 0.5 %; ± 0.1 %	± 1 %; ± 0.5 %; ± 0.1 %				
Temperature coefficient	± 25 ppm/K	± 50 ppm/K; ± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K				
Rated dissipation, P_{70} ⁽¹⁾	0.075 W	0.130 W	0.210 W	0.260 W	0.520 W	0.520 W
Operating voltage, U_{max} , AC_{RMS} or DC	25 V	75 V	100 V	150 V	200 V	200 V
Permissible film temperature, $\vartheta_{F max}$ ⁽¹⁾						



MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION				
OPERATION MODE		GENERAL	POWER	ADVANCED
Rated dissipation, P_{70}	TNPW0201 e3	0.050 W	0.075 W	-
	TNPW0402 e3	0.070 W	0.105 W	0.130 W
	TNPW0603 e3	0.110 W	0.170 W	0.210 W
	TNPW0805 e3	0.140 W	0.220 W	0.260 W
	TNPW1206 e3	0.270 W	0.420 W	0.520 W
	TNPW1210 e3	0.330 W	0.500 W	0.520 W
Operating temperature range		-55 °C to 125 °C	-55 °C to 155 °C	-55 °C to 175 °C
Permissible film temperature, ϑ_F max.		125 °C	155 °C	175 °C
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ after:	TNPW0201 e3	22 Ω to 40 k Ω		
	TNPW0402 e3	10 Ω to 100 k Ω		
	TNPW0603 e3	1 Ω to 332 k Ω		
	TNPW0805 e3	1 Ω to 1 M Ω		
	TNPW1206 e3	1 Ω to 2 M Ω		
	TNPW1210 e3	1 Ω to 3.01 M Ω		
	1000 h	≤ 0.05 %	≤ 0.10 %	≤ 0.20 %
	8000 h	≤ 0.10 %	≤ 0.20 %	-
	225 000 h	≤ 0.30 %	≤ 0.60 %	-

Note

- The presented operation modes do not refer to different types of resistors, but actually show examples of different loads, that lead to different film temperatures and different achievable load-life stability (drift) of the resistance value. A suitable low thermal resistance of the circuit board assembly must be safeguarded in order to maintain the film temperature of the resistors within the specified limits. Please consider the application note "Thermal Management in Surface-Mounted Resistor Applications" (www.vishay.com/doc?28844) for information on the general nature of thermal resistance



TEMPERATURE COEFFICIENT AND RESISTANCE RANGE					
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES	
TNPW0201 e3	± 25 ppm/K	± 0.5 %	22 Ω to 40 k Ω	E24; E192	
		± 0.1 %	22 Ω to 25 k Ω		
TNPW0402 e3	± 50 ppm/K	± 1 %	10 Ω to 100 k Ω	E24; E96	
		± 0.5 %		E24; E192	
		± 0.1 %	47 Ω to 100 k Ω		
	± 25 ppm/K	± 1 %	10 Ω to 100 k Ω	E24; E96	
		± 0.5 %		E24; E192	
		± 0.1 %	47 Ω to 100 k Ω		
	± 15 ppm/K	± 0.1 %			
	± 10 ppm/K				
TNPW0603 e3	± 50 ppm/K	± 1 %	1 Ω to 332 k Ω	E24; E96	
		± 0.5 %		E24; E192	
		± 0.1 %	3.5 Ω to 332 k Ω		
	± 25 ppm/K	± 1 %	1 Ω to 332 k Ω	E24; E96	
		± 0.5 %		E24; E192	
		± 0.1 %	3.5 Ω to 332 k Ω		
	± 15 ppm/K	± 0.1 %	47 Ω to 332 k Ω		
	± 10 ppm/K				
TNPW0805 e3	± 50 ppm/K	± 1			

**PACKAGING**

TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
TNPW0201 e3	ET2 = EI	5000	Paper tape according IEC 60286-3, Type 1a	8 mm	2 mm	Ø 180 mm / 7"
	ET7 = ED	10 000				
TNPW0402 e3	ET2 = EI	5000				
	ET7 = ED	10 000				
TNPW0603 e3 TNPW0805 e3 TNPW1206 e3 TNPW1210 e3	ET1 = EA	5000			4 mm	Ø 180 mm / 7"
	ET6 = EC ⁽¹⁾	20 000			4 mm	Ø 330 mm / 13"

Note

⁽¹⁾ 20 000 pieces packaging is available only for resistors with TCR ± 25 ppm/K and ± 50 ppm/K

PART NUMBER AND PRODUCT DESCRIPTION

Part Number: TNPW12061K32DEEA

T	N	P	W	1	2	0	6	1	K	3	2	D	E	E	A		
TYPE / SIZE		RESISTANCE		TOLERANCE		TCR		PACKAGING		SPECIAL							
TNPW0201 TNPW0402 TNPW0603 TNPW0805 TNPW1206 TNPW1210		R = decimal K = thousand M = million (4 digits)		B = ± 0.1 % D = ± 0.5 % F = ± 1.0 %		H = ± 50 ppm/K E = ± 25 ppm/K X = ± 15 ppm/K Y = ± 10 ppm/K		ED EI EA EC (E.. = lead (Pb)-free)		Up to 2 digits Blank = standard 0H = single lot date code							

Product Description: TNPW1206 1K32 0.5 % T-9 ET1

DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of special metal alloy is deposited on a high grade ceramic substrate (Al_2O_3) and conditioned to achieve the desired temperature coefficient. Specially designed inner contacts are deposited on both sides. A special laser is used to achieve the target value by smoothly fine trimming the resistive layer without damaging the ceramics. A further conditioning is applied in order to stabilize the trimming result. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure matte tin on nickel plating. The result of the determined production is verified by an extensive testing procedure and optical inspection performed on 100 % of the individual chip resistors. This includes full screening for the elimination of products with a potential risk of early life failures (feasible for $R \geq 10 \Omega$). Only accepted products are laid directly into the tape in accordance with **IEC 60286-3, Type 1a** ⁽¹⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapour phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system ⁽²⁾.

The resistors are RoHS-compliant, the pure matte tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽³⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽⁴⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽⁵⁾ for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)



Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.


RELATED PRODUCTS

The TNPW with SnPb termination plating is designed for those applications, where lead bearing terminations are mandatory.


**FUNCTIONAL PERFORMANCE**

PERFORMANCE IN SULFUR-CONTAINING AMBIANCE		
TEST NAME	HUMID SULFUR VAPOR TEST FOS-90	DRY SULFUR TEST FOS-105
Reference specification	ASTM B 809	ANSI/EIA-977
Test conditions (temperature, humidity)	90 °C ± 2 °C 76 % to 95 % RH	105 °C ± 2 °C RH not specified, not applicable
Aggressive agent	Sulfur (saturated vapor)	Sulfur, sublimed
Failure criteria in VI under magnification	Silver sulfide growth: length shall be < 50 µm	Not applicable
Failure criteria in electrical test	$\leq (\pm 1 \% R + 0.05 \Omega)$	$\leq (\pm 1 \% R + 0.05 \Omega)$
Test duration	1000 h	1000 h

**Derating - General Operation****Derating - Power Operation**




Derating - Advanced Operation




Maximum pulse load, single pulse; applicable if $\bar{P} \rightarrow 0$ and $n \leq 1000$ and $\dot{U} \leq \dot{U}_{\max.}$; for permissible resistance change $\pm (0.5 \% R + 0.05 \Omega)$

Single Pulse




Maximum pulse load, continuous pulse; applicable if $\bar{P} \leq P(\vartheta_{\text{amb}})$ and $\dot{U} \leq \dot{U}_{\max.}$; for permissible resistance change $\pm (0.5 \% R + 0.05 \Omega)$

Continuous Pulse




Maximum pulse voltage, single and continuous pulses; applicable if $\hat{P} \leq \hat{P}_{max.}$;
for permissible resistance change $\pm (0.5 \% R + 0.05 \Omega)$

Pulse Voltage




Pulse load rating in accordance with EN 60115-1 clause 4.27; 1.2 μ s/50 μ s;
5 pulses at 12 s intervals; for permissible resistance change $\pm (0.5 \% R + 0.05 \Omega)$

1.2/50 Pulse




Pulse load rating in accordance with EN 60115-1 clause 4.27; 10 μ s/700 μ s;
10 pulses at 1 minute intervals; for permissible resistance change $\pm (0.5 \% R + 0.05 \Omega)$

10/700 Pulse




In accordance with IEC 60195

Current Noise Voltage Ratio



In accordance with IEC 60195


Non-Linearity









HF Performance ⁽¹⁾

Note

⁽¹⁾ Typical figures, HF-characteristic also depends on termination and circuit design



HF Performance ⁽¹⁾


HF Performance ⁽¹⁾

HF Performance ⁽¹⁾

HF Performance ⁽¹⁾

HF Performance ⁽¹⁾

HF Performance ⁽¹⁾

HF Performance ⁽¹⁾
Note
⁽¹⁾ Typical figures, HF-characteristic also depends on termination and circuit design

**TEST AND REQUIREMENTS**

All tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8, sectional specification

EN 140401-801, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-801. The detail specification EN 140401-801 does not cover case size 0201. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA / ECA-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C

Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar)

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days).


The components are mounted for testing on printed circuit boards in accordance with EN 60115-8, 2.4.2, unless otherwise specified.

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
			Stability for product types:	
			TNPW0201 e3	22 Ω to 40 k Ω
			TNPW0402 e3	10 Ω to 100 k Ω
			TNPW0603 e3	1 Ω to 332 k Ω
			TNPW0805 e3	1 Ω to 1 M Ω
			TNPW1206 e3	1 Ω to 2 M Ω
			TNPW1210 e3	10 Ω to 3.01 M Ω
6.1	-	Resistance		

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
			Stability for product types:	
			TNPW0201 e3	22 Ω to 40 k Ω
			TNPW0402 e3	10 Ω to 100 k Ω
			TNPW0603 e3	1 Ω to 332 k Ω
			TNPW0805 e3	1 Ω to 1 M Ω
			TNPW1206 e3	1 Ω to 2 M Ω
			TNPW1210 e3	10 Ω to 3.01 M Ω
10.4	78 (Cab)	Damp heat, steady state	(40 $\pm$ 2) $^{\circ}$ C; 56 days; (93 $\pm$ 3) % RH	$\pm$ (0.1 % R + 0.01 Ω)
10.5	67 (Cy)	Damp heat, steady state accelerated: general operation mode	(85 $\pm$ 2) $^{\circ}$ C (85 $\pm$ 5) % RH $U = \sqrt{0.1 \times P_{70} \times R}$; $U \leq 0.3 \times U_{max.}$; 1000 h	$\pm$ (0.1 % R + 0.01 Ω)
-	1 (Ab)	Cold	-55 $^{\circ}$ C; 2 h	$\pm$ (0.05 % R + 0.01 Ω)
10.1	14 (Na)	Rapid change of temperature	30 min at LCT and 30 min at UCT; LCT = -55 $^{\circ}$ C; UCT = 155 $^{\circ}$ C; 1000 cycles	$\pm$ (0.1 % R + 0.01 Ω)
8.1	-	Short time overload: general operation mode	$U = 2.5 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{max.}$; whichever is the less severe; 5 s	$\pm$ (0.05 % R + 0.01 Ω)
		Short time overload: power operation mode	$U = 2.5 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{max.}$; whichever is the less severe; 5 s	$\pm$ (0.1 % R + 0.01 Ω)
8.2	-	Single pulse high voltage overload: general operation mode	Severity no. 4: $U = 10 \times \sqrt{P_{70} \times R}$ or	

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
			Stability for product types:	
			TNPW0201 e3	22 Ω to 40 k Ω
			TNPW0402 e3	10 Ω to 100 k Ω
			TNPW0603 e3	1 Ω to 332 k Ω
			TNPW0805 e3	1 Ω to 1 M Ω
			TNPW1206 e3	1 Ω to 2 M Ω
			TNPW1210 e3	10 Ω to 3.01 M Ω
8.5	-	Electro static discharge (human body model)	IEC 61340-3-1 ⁽¹⁾ ; 3 pos. + 3 neg. (equivalent to MIL-STD-883, method 3015) TNPW0201 e3: 250 V TNPW0402 e3: 400 V TNPW0603 e3: 1000 V TNPW0805 e3: 1500 V TNPW1206 e3: 2000 V	$\pm (0.5 \% R + 0.05 \Omega)$
9.11	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s ² ; 7.5 h	$\pm (0.05 \% R + 0.01 \Omega)$ no visible damage
11.1	58 (Td)	Solderability	Solder bath method; SnPb40; non-activated flux (215 $\pm$ 3) °C; (3 $\pm$ 0.3) s	Good tinning (≥ 95 % covered); no visible damage
			Solder bath method; SnAg3Cu0.5 or SnAg3.5; non-activated flux (235 $\pm$ 3) °C; (2 $\pm$ 0.2) s	
11.2	58 (Td)	Resistance to soldering heat	Solder bath method; (260 $\pm$ 5) °C; (10 $\pm$ 1) s ⁽³⁾	$\pm (0.02 \% R + 0.01 \Omega)$
11.3	45 (XA)	Component solvent resistance	Isopropyl alcohol + 50 °C; method 2	No visible damage
9.7	21 (Ue ₃)	Shear (adhesion)	TNPW0201 e3: 2 N	No visible damage

DIMENSIONS



DIMENSIONS AND MASS					
TYPE / SIZE	L (mm)	W (mm)	H (mm)	T _t / T _b (mm)	MASS (mg)
TNPW0201 e3	0.6 ± 0.05	0.3 ± 0.05	0.23 ± 0.03	0.12 ± 0.05	0.14
TNPW0402 e3	1.0 ± 0.05	0.5 ± 0.05	0.35 ± 0.05	0.2 ± 0.10	0.65
TNPW0603 e3	1.55 ± 0.05	0.85 ± 0.10	0.45 ± 0.10	0.3 ± 0.20	2
TNPW0805 e3	2.0 ± 0.1	1.25 ± 0.15	0.45 ± 0.10	0.4 ± 0.20	5.5
TNPW1206 e3	3.2 + 0.1 / - 0.2	1.6 ± 0.15	0.55 ± 0.10	0.5 ± 0.25	10
TNPW1210 e3	3.2 + 0.1 / - 0.2	2.45 ± 0.15	0.60 ± 0.15	0.5 ± 0.25	16

SOLDERING RECOMMENDATIONS

For recommended solder pad dimensions please refer to www.vishay.com/doc?28950.

For recommended soldering profiles please refer to www.vishay.com/doc?31090.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.