



6

Technical drawing of a plate with the following dimensions and features:

- Overall width: 100
- Overall thickness: 1.2
- Number of holes: 8
- Distance between hole centers: $(N-1) \times 2.54$
- Maximum total length: $N \times 2.54 \text{ MAX}$
- Note: NOTE 5
- Flange width on the right: 2.4



Technical drawing showing a side view of a bolted connection. The drawing includes dimensions for the bolt spacing (2.54), the bolt diameter (0.62 SQUARE), and the bolt head diameter (2.5).

[illegible]



FCIconnect.com

Copyright FCI

PLATING

- 1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
4 = 2µm TIN MIN FULL PLATED
5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
G = 0.76µm FULL GXT
S = 0.38µm FULL GXT
- 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

PRODUCT SPECIFICATIONS

PIN	STYLE	MATING	SOLDER	DIM "C"
01		5.72	2.57	1.5
02		5.72	5.11	1.5
07		5.72	5.11	3.9
13		5.72	3.45	1.5
18		5.84	3.05	1.5
22		11.71	3.2	1.5
24		6.75	2.85	1.5
25		8.07	3.05	1.5
26		8.2	12.6	1.5
27		5	3.9	1.5
28		3.1	3.1	1.5
29		9.7	2.90	1.5
30		8.30	4.40	1.5
31		11.70	2.80	1.5
32		8.90	3.05	1.5
33		10.20	3.05	1.5
34		10.00	3.25	1.5
35		5.72	12.73	1.5
36		N/A		
37		N/A		
38		8.51	5.51	1.5
39		9.80	9.30	1.5
40		8.13	2.54	3.90
41		14.20	3.05	1.5
42		9.00	7.20	1.5
43		8.08	2.79	1.5
44		15.70	2.79	1.5

mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
AG	F12-0095	LMU	12.10.25	angles	linear	.X ±0.3		UNSHR.HEADER RA SR TMT					
AH	B-15093	JCO	13.06.28			.XX ±0.15							
AJ	B-15388	LMU	13.07.31			.XXX ±0.05							
						scale 5:1		dwg no					
AK	B-16178	JCO	13.10.31	dr	D.LE	01.01.24				sheet 2 of 2		size	
AL	B-17109	JCO	14.03.06	enr	JM.C	01.01.24				77315		A3	
AM	B-18916	LMU	14.09.26	chr	JM.C	01.01.24							
				appd	JF.N	01.01.24				type CUSTOMER		Drawing	
sheet index		revision sheet											