

1-1102241-7 Product Details

[!\[\]\(003082e50e3009141f59bd5df831749f_img.jpg\) Share](#) [!\[\]\(f439ede8735757e3190eab35e168f1de_img.jpg\) Print](#) [!\[\]\(f5c165e0bd35116675db6686a30b1fea_img.jpg\) Email](#)



1-1102241-7

TE Internal Number: 1-1102241-7



HTS Connectors and Accessories

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- HB.6 Series
- Accessory
- Accessory Type = Hood
- Product Size = 3
- Locking Device Type = Side Clip at Housing Bottom

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Hood HB.6](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Accessory
- Accessory Type = Hood
- Product Size = 3
- [Thread Size](#) = PG16
- Finish = Silver Gray

Body Features:

- Entry Style = Top
- Dimensions (L x H x W) (mm [in]) = 74.0 x 48.0 x 43.0 [2.92 x 1.89 x 1.69]
- Material = Die Cast Aluminum

Contact Features:

- Corrosion Protected = No

Configuration Features:

- Locking Device Type = Side Clip at Housing Bottom

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Packaging Features:

- Packaging Method = Loose Piece
- Packaging Quantity = 5

Other:

- Series = HB.6
- Brand = HTS
- Comment = Hood assembly includes cable adapter.

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

1999

(C) COPYRIGHT 1998 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

A1

DIST

P

LTR






REVISIONS

A4

DESCRIPTION

DATE DWN APVD

06.Mar.2008 SP TS



1	-	Gland fitting PG16	Brass	Nickel plated	4	
-	1	Cable connection round PG16	Brass	Nickel plated	3	
1	-	Hood HB6.Sto	Aluminium	Aluminium oxide	Black	2
-	1	Hood HB6.Sto	Aluminium	-	Grey	1
2-7	1-7	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM NO NOTES

ORDERING TEXT

HB.6.Sto.1.16

HB-K.6.Sto.1.16

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

±

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

n. ISO 805: n. ISO 2768-MH-E:

n. DIN 16901-120

APVD

Schneider 20.01.99

CHK 20.01.99

Schweiger 20.01.99

PRODUCT SPEC

114-74004

APPLICATION SPEC

108-74001/74003

WEIGHT

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV A4

Tyco Electronics Tyco Electronics,AMP,GmbH
D-53819,Neunkirchen,Germany

NAME Hood HB.6

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C- 1102241