

HBL4770C -- Twist-Lock Plug



2P3W, 15A 277V AC, L7-15P, Black & White Nylon

Product Specifications

Product Type	 Twist-Lock Devices
Product Item	Plug
Wiring Scheme	2 Pole, 3 Wire Grounding
Amperage	15A
Voltage	277V AC
NEMA Configuration	L7-15P
Item Style	Insulgrip
Device Color	Black/White
Horsepower	2
Cord Dia.	.230"-.720" (5.8-18.3)
Blade Holder Material	Natural White Nylon
Terminal Retainer Material	Clear polycarbonate
Housing Material	Black nylon
Cord Clamp Material	Natural (white) nylon

Blade Material	Brass
Terminal Clamp Material	Cold rolled steel-nickel-plated
Terminal Screw Material	#8-32 Brass (white finish on neutral screw when used)
Ground Screw Material	Brass (green finish)
Cord Clamp Screw Material	Steel-zinc-plated
Body Holding Screw Material	Steel-zinc-plated
Ratings	Molded into face.
Catalog No.	Permanently ink marked on cord clamp.
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	15A-#14AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Listings	UL/CSA
Certified	UL2306 OEM and replacement use on convention center flat cable cord sets.
Catalog Page	Click here for catalog page B11
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-B
UPC Number	78358517170
Weight in LBs	0.15



NEMA L7-15P
15A 277V AC
UL/CSA
2 HP

NEMA
Configuration

Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031



Wiring Device-Kellems