









RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

METRIC

.040	1.02		
.035	0.89	.700	17.78
.032	0.81	.535	13.59
.025	0.64	.310	7.87
.020	0.51	.295	7.49
.015	0.38	.225	5.72
.010	0.25	.200	5.08
.008	0.20	.140	3.56
.007	0.18	.130	3.30
.005	0.13	.125	3.18
.003	0.08	.100	2.54
.001	0.03	.063	1.60
.000	0.00	.050	1.27
IN	MM	IN	MM

CONVERSION TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 910-97 B. LEWIS		 TE Connectivity	
		GIR 910-97 R. SWING			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE STRAIGHT POST, TIN PLATED,	
		APVD			
		PRODUCT SPEC			
		APPLICATION SPEC			
		SIZE			
MATERIAL	FINISH	WEIGHT	A1 00779		C-644178
				SCALE: R:1 SHEET 1 OF 1 REV. K:1	
CUSTOMER DRAWING					