




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

B

A

PRODUCT NUMBER
51965-A00CCC00EF-- NOTE 1



1 | 2

Pro/E

3 |

cage code 22526

4

mat'l code				NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date					COPY		projection	title	product family	code
A	V04-0387	TAB	04/16/04	linear		.XX±.01/0.X±0.3					VERTICAL HEADER w/ GUIDE PIN SIGNAL	PWRBLADE	213
B	DG05-0563	RYAN	12/30/05			.XXX±.005/0.XX±0.13						size	sheet
C	DG10-0262	Anson	07/15/10	angles		.XXX±.0020/.XXX±.051						dwg no	1 of 3
						0°±2°							
				dr	T. BRUNGARD	04/16/04							
				enr	M. GRAY	04/16/04							
				chr	M. GRAY	04/16/04							
				appd	M. GRAY	04/16/04							
sheet index	revision sheet	C	C	C									
		1	2	3									

B

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

A

B

1 | 2

3 |

4

PRODUCT NUMBER		DIM		LENGTH FORMULAS (SEE NOTE 8)	
51965-A00CCC00EF-- NOTE 1		DIM "A"		.100 [2.54] x (CCC/4) + .650 [16.51] (NOTE 8)	
		DIM "B"		.100 [2.54] x (CCC/4) + .350 [8.89]	
		DIM "C"		.100 [2.54] x (CCC/4) + .300 [7.62]	
		DIM "D"		.100 [2.54] x (CCC/4) + .680 [17.27]	

CONNECTOR NOTES		PCB NOTES:	
1. PRODUCT NUMBER CODE: 51965 - A 00 CCC 00 E F LF		7 MANUFACTURE'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.	
NO THIS SUFFIX:100U"/2.54um SnPb ON PCB INTERFACE ADD THIS SUFFIX:78u"/2.00um Sn ON PCB INTERFACE RETENTION TO PCB (NOTE 6) TAIL OPTIONS (NOTE 5) ALWAYS "00" NUMBER OF SIGNAL CONTACTS (NOTE 4) ALWAYS "00" PLATING (NOTE 3) BASE NUMBER		8 THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART IS 8.00 [203.2].	
2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH TEMP THERMOPLASTIC SIGNAL CONTACT MATERIAL: COPPER ALLOY		9 PRODUCT SPECIFICATION GS-12-149.	
3. PLATING: 1=SEE PRINT 10064183 FOR PLATING SPEC OF 51965-100CCC00EF AND 51965-100CCC00EFLF RESPECTIVELY		10. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH) ASME Y14.5m, 1994 UNLESS OTHERWISE SPECIFIED.	
4 SIGNAL CONTACT, 004 TO 148 AVAILABLE.		11. ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.	
5 TAIL OPTIONS: A = 0.135 +0.015/-0.010 [3.43 +0.38/-0.25] SOLDER TO BOARD B = 0.165 +0.015/-0.010 [4.19 +0.38/-0.25] SOLDER TO BOARD C = 0.165 +0.015/-0.010 [4.19 +0.38/-0.25] PRESS FIT		12. ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF 0.004 [0.10]	
6 RETENTION TO PCB OPTIONS: A = BOARD LOCK (REQUIRES 0.098 +0.002/-0.001 [2.49 +0.05/-0.03] THUR HOLE IN PCB). RECOMMENDED ON SYMMETRIC CONNECTORS. BOARD LOCK TO BE USED IN CONJUNCTION WITH A .092 PCB OR THICKER. C = NO RETENTION FEATURE.		13. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE	
		14. Ø0.098 [2.49] THROUGH HOLES ARE UNPLATED.	
		15. Ø0.0453±0.0010 [1.151±0.025] DRILLED HOLES PLATED WITH 0.0003 [0.008] MIN SnPb OVER 0.001 [0.03] TO 0.003 [0.08] Cu PLATING TO ACHIEVE A Ø0.040±0.003 [1.02±0.07] HOLE.	
		16. FOR PRESSFIT APPLICATION USE FCI CAM TOOL 430169-XXX.	

mal'ti code				NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date			.XX±.01/0.X±0.3	COPY			www.fciconnect.com	
C				linear		.XXX±.005/0.XX±0.13	projection		title VERTICAL HEADER w/ GUIDE PIN SIGNAL		
				angles		.XXX±.0020/.XX±.051					
				dr	T. BRUNGARD	04/16/04		INCH/MM	product family	PWRBLADE	code
				enrg	M. GRAY	04/16/04			size	dwg no	213
				chr	M. GRAY	04/16/04					sheet
				appd	M. GRAY	04/16/04					2 OF 3
sheet index	revision sheet										

Pro/E		3		cage code		4	
				22526			

A


B

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51965-A00CCC00EF-- NOTE 1



SECTION A-A



SECTION C-C



RECOMMENDED PCB LAYOUT

NOTE 2				TOLERANCES UNLESS OTHERWISE SPECIFIED		CUSTOMER		FCI	
ltr	ecr no.	dr	date	linear	.XX±.01/.X±0.3	COPY		www.fciconnect.com	
C				linear	.XXX±.005/.XX±0.13	projection		title VERTICAL HEADER w/ GUIDE PIN SIGNAL	
				linear	.XXX±.0020/.XXX±.051	projection			
				angles	0°±2°	projection			
				dr	T. BRUNGARD 04/16/04	INCH/MM		product family PWRBLADE code 213	
				enr	M. GRAY 04/16/04	scale		size dwg no 51965 sheet 3 OF 3	
				chr	M. GRAY 04/16/04	1:1			
				appd	M. GRAY 04/16/04				
sheet index	revision sheet							cage code 22526	

Pro/E