

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

2000

© COPYRIGHT 2000

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

PN 0-1 As Shown


Contact arrangement
view from connecting sideContact arrangement
view from termination side

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
A1			B1	ECR-10-021590	26.10.2010	SR OH

NOTES

- SUITABLE CRIMP CONTACTS: SERIES HN.D
CUSTOMER DRAWING: 1105050
OUTER DIMENSIONS OF INSULATION: MAX. Ø4mm
- SUITABLE MODULE FIXING FRAME: SERIES HVS SIZE 3 TO 8
CUSTOMER DRAWING: 1103250
- SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 1102855
- SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 1102855
- STANDARDS:
DIN EN 61984; DIN EN 60664-1
-  POLARIZATION RIPS
-  MARKING OF POLARIZATION ACCORDING TO MARKING OF
MODULE FRAME
- PACKAGING:
10 SETS IN A CARTON, PRE-MOUNTED

PN 0-1 As Shown




SCALE 1:1

B1 9 10

1	FEMALE INSERT	PC-GF20	LIGHT GREY	21
QTY	DESCRIPTION	MATERIAL	COLOR	ITEM NO
PN 0-1 / HVS-HN.D.17.Bu.C				

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		ISO 8075 DIN ISO 2768 mH-E DIN 36901-120	
	0 PLC	±	±
	1 PLC	±	±
	2 PLC	±	±
	3 PLC	±	±
	4 PLC	±	±
ANGLES		±	
MATERIAL		FINISH	
			

DWN	20.02.2006
CHK	20.02.2006
APVD	20.02.2006
PRODUCT SPEC	108-74083
APPLICATION SPEC	114-74085
WEIGHT	
CUSTOMER DRAWING	

 Tyco Electronics		Tyco Electronics AMP GmbH 53757 Sankt Augustin, Germany		
NAME FEMALE INSERT HVS-HND.17.BU.C				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	Ⓒ-1103279		
SCALE		SHEET	OF	REV
2:1		1	1	B1