

FREQUENCY RANGE	OVERALL STABILITY OPTIONS
400kHz ~ 160MHz	9710A = 25PPM 9710B = 50PPM 9710C = 100PPM

Note 1 Stability options are inclusive of: Calibration Tolerance at 25°C, Operating Temperature Range, Supply Voltage Change, Load Change, Ageing, Shock & Vibration.

Parameter	Code	Value	Unit	Remarks
Storage Temperature Range	Tstg	-65 to +125	°C	
Operating Temperature Range	Top	0 to +70	°C	
Input Voltage	V _{cc}	+5	V DC	10%
Max Input Current	ICC	20 40 50	mA Max	500 kHz to 20MHz 20.1MHz to 80MHz 80.1MHz to 160MHz
Duty Ratio	SY	50:50 10%	%	At 50% V _{DD}
"O" Level	V _{OL}	0.5	V DC	Max
"1" Level	V _{OH}	4.5	V DC	Min
Max Rise/Fall Time	Tr:Tf	10 6 4	nS Max	500 kHz to 20MHz 20.1MHz to 70MHz 70.1MHz to 100MHz
Start-Up Time	TSTART	5	mS	
Fan-Out (Load)		15pF Min 1-10 TTL		HCmos TTL

MECHANICAL

Drop Test - Drop Module onto a hard wooden surface from 20cm 3 times

Shock Test - 1500g (Peak) 0.35mS (1/2Sine Wave) 5 Times

Vibration Test - Vibrations with an amplitude of 3mm and a sweep from 10-55 Hz duration 1 minute shall be applied for 2 hours in each of the x,y, & z axes

ENVIRONMENTAL

Solder Heat - Immerse pins to within 1mm of glass stand-offs in solder bath of 280°C ±10°C for 10 secs

Life Test - After exposure to +125°C (Power Applied) for 1000 Hrs

Cold Resistance - After exposure to -40°C for 2 hrs


Humidity - After exposure to +40°C 90-95% RH for 48 Hrs

Thermal Shock - After 10 cycles of exposure to -55°C & 125°C with 10mins exposure at each extreme

Fine Leak - Helium leak detector, pressure 5kg.f/cm³ for 2 Hrs, leakage less than 1×10^{-8} Atm.cc/Sec

TITLE: AEL 9710 Series Oscillator 14-Pin DIL UNIVERSAL O/P (Hcmos & TTL) 400kHz to 160MHz


AEL Stock Code	Issue Number	Issue Date	Approved
	4	17/06/97	GR



Pin Connections

Pin 1 = NC
 Pin 7 = Ground
 Pin 8 = Output
 Pin 14 = +V DC

Waveform




AEL Crystals Limited
www.aelcrystals.co.uk



Module 'D' Airtech 2
 Jenner Road, Crawley
 W. Sussex. RH10 2GA

Tel: 01293 524245
 Fax: 01293 524888

© Not to be reproduced without permission of AEL Crystals Ltd