



Auxiliary contacts

Part no.
Article no.

HI11-P1/P3E
061813



Powering Business Worldwide™

Delivery programme

Product range			Accessories
			Auxiliary contact
			Late-break switching-on behavior, early-make switching-off behavior. The N/O is always connected as a load-shedding contact. For left and/or right side mounting
Contacts			1 N/O, 1 N/C
For use with			P1-.../E, .../EA..., .../EZ P3-.../E, .../EA
Rated uninterrupted current	I_u	A	10

Approvals

Product Standards
UL File No.
UL CCN
CSA File No.
CSA Class No.
NA Certification

UL 508; CSA-C22.2 No. 14-05; IEC/EN 60947-5; CE marking
E36332
NLRV
12528
3211-05
UL listed, CSA certified

Auxiliary contacts

Standards			Control circuit isolators to IEC/EN 60947-5 
Rated insulation voltage	U_i	V AC	500
Rated uninterrupted current	I_u	A	10
Rated operational current	I_e	A	
AC-15			
230 V	I_e	A	6
DC-13	I_e		
125 V	I_e	A	1.1
250 V	I_e	A	0.55
Short-circuit rating			
Maximum fuse		A gG/ gL	10
Terminal capacities		mm ²	
Solid		mm ²	0.75 - 2.5
Flexible with ferrule to DIN 46228		mm ²	0.5 - 1.5
Tightening torque		Nm	0.6
Control circuit reliability at 24 V DC, 10 mA	Fault probability	H_F	$< 10^{-5}$, < 1 fault in 100 000 operations

Technical data ETIM 4.0

Number of auxiliary contacts as normally open contact			0
Number of auxiliary contacts as normally closed contact			0
Rated permanent current I_u		A	0
Number of poles			0
Conditioned rated short-circuit current I_q		kA	0
Degree of protection (IP), front side			-
Number of auxiliary contacts as change-over contact			0
Interlockable			No
Motor drive integrated			No
Connection type main current circuit			Screw connection
Version as emergency stop installation			No
Type of control element			-
Version as main switch			No

