


# RUGGED RELIABLE MICRO SOCKETS

(1.00 mm) .0394" PITCH • CLM/MLE SERIES



## CLM

### Mates:

FTM, FTMH, MW

## MLE

### Mates:

FTM, FTMH, MW

## SPECIFICATIONS

**Insulator Material:** Black LCP

**Contact Material:**

CLM: Phosphor Bronze

MLE: BeCu

**Plating:**

CLM: Au or Sn over

50  $\mu$ " (1.27  $\mu$ m) Ni

MLE: Au over 10  $\mu$ " (0.25  $\mu$ m) Ni

**Operating Temp Range:**

-55 °C to +125 °C

**Current Rating (CLM/FTMH):**

3.1 A per pin

(2 pins powered)

**Current Rating (MLE/FTMH):**

2.9 A per pin (2 pins powered)

**Max Cycles:**

CLM: 100 with 10  $\mu$ " (0.25  $\mu$ m) Au

**Voltage Rating:**

CLM: 270 VAC/382 VDC

MLE: 310 VAC/438 VDC

**Insertion Depth:**

CLM:

Top Entry = (1.40 mm) .055" min.,

Bottom Entry =

(2.41 mm) .095" min.

(Add board thickness for

correct post OAL)

MLE:

(1.63 mm) .064" to



(3.18 mm) .125" with

(0.38 mm) .015" wiper,

pass-through, or (2.44 mm) .096"

minimum for bottom entry

**TIGER  
CLAW  
CONTACT**



## MLE

- 1

NO. PINS  
PER ROW

- 01

PLATING  
OPTION

- DV

OPTIONS

02 thru 50

**Lead-Free Solderable:**

Yes

**SMT Lead Coplanarity:**

(0.10 mm) .004" max (02-25)



(0.15 mm) .006" max (26-50)\*

\*(.004" stencil solution

may be available; contact

ipg@samtec.com)

**TIGER  
BEAM  
CONTACT**



## ALSO AVAILABLE

Contact Samtec

Alignment pin

Other Gold plating options



### Note:

Some lengths, styles and options are non-standard, non-returnable.

[samtec.com?CLM](http://samtec.com?CLM) or [samtec.com?MLE](http://samtec.com?MLE)

F-226

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.