

Encoder 11mm Size Metal Shaft Reflow Type

EC11J Series



Compact and highly reliable type available in many varieties.



Typical Specifications

Items	Specifications
Rating	10mA 5V DC
Operating life	100,000cycles 500,000cycles 1,000,000cycles
Operating temperature range	-40°C to +85°C

Product Line

Structure	Actuator configuration	Actuator length (mm)	Torque (mN·m)	Number of detent	Number of pulse	Push-on switch	Travel of push-on switch (mm)	Operating life (cycles)	Minimum order unit (pcs.)	Product No.	Drawing No.
Reflow	Flat	20	12±5	18	9	Without	—	100,000	600	EC11J0920402	1
				30	15					EC11J1520402	
				18	9	With	0.5			EC11J0924411	2
				30	15		1.5			EC11J1524413	
				18	9					EC11J0925403	
				30	15					EC11J1525402	
				18	9	Without	—	500,000		EC11J0920602	1
				30	15					EC11J1520602	
				18	9	With	0.5			EC11J0924602	2
				30	15		1.5			EC11J1524604	
				18	9					EC11J0925602	
				30	15					EC11J1525602	
				18	9	Without	—	1,000,000		EC11J0920802	1
				30	15					EC11J1520803	
				18	9	With	0.5			EC11J0924802	2
				30	15		1.5			EC11J1524802	
				18	9					EC11J0925802	
				30	15					EC11J1525802	

Notes

1. The operating temperature range for automotive applications can be raised upon request. Please contact us for details.
2. Please place purchase orders per minimum order unit N (integer).

Packing Specifications

Tray

Number of packages (pcs.)		Export package measurements (mm)
1 case /Japan	1 case /export packing	
300	600	369 × 283 × 263

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Metal
Shaft

Insulated
Shaft

Hollow
Shaft

Ring
Type








Automotive
Use

Refer to P.212 for product varieties.
Refer to P.217 for product specifications.
Refer to P.212 for soldering conditions.

Dimensions

Unit:mm

No.	Photo	Style	PC board mounting hole dimensions (Viewed from mounting side)
1	Reflow applicable parts 		 EC11J09 Type only EC11J15 Type only PC board mounting detail A slant line part hows the solder land black part: Do not solder and wiring for electrical contact
2	Reflow applicable parts with push-on switch (travel 0.5mm/1.5mm) 		 EC11J09 Type only EC11J15 Type only PC board mounting detail A slant line part hows the solder land black part: Do not solder and wiring for electrical contact

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Metal
Shaft

Insulated
Shaft

Hollow
Shaft


Ring
Type





Automotive
Use

Product Specifications



Output Wave



Circuit Diagram




Sliding Noise



Attached Parts

EC11B Series

Unit:mm



List of Varieties

Type		Metal shaft			
		11mm size		20mm size	
Series		EC11K	EC11J	EC20A/RK203	EM20B
Photo					
Output		Incremental			
Outline specifications	Shaft types	Single-shaft			
	Operating direction	Vertical			
	Number of pulse/ Number of detent	9/18 15/30		18/18	40/40
	Push switch (Travel mm)	Without With (0.5, 1.5)		Without With (1.5)	Without With (0.5)
	Optional function				Display function
Dimensions (mm)	W	11.7		20.2	20
	D	12	14.2	19.2	22.25
	H	4.5		10	13
Soldering	Manual soldering	350°C max. 3s max.			
	Dip soldering	260±5°C, 3±1s		260±5°C, 5±1s	260°C max. 3s max.
	Reflow soldering		Please see P.212		
Operating temperature range		-40°C to +85°C			-10°C to +70°C
Automotive use		○	○	○	—
Maximum operating current (Resistive load)		10mA			—
Electrical performance	Output signal	Output of A and B signals, proportionate to phase difference			V _H : +4.0V min. V _{LO} : 0.5V max. (Isink=5mA)
	Output wave	Please see P.217			—
	Output phase				A, B (Squarewave)
	Sliding noise	Please see P.217			—
	Insulation resistance	100MΩ min. 250V DC		10MΩ min. 50V DC	100MΩ min. 250V DC
	Voltage proof	300V AC for 1minute		50V AC for 1minute	300V AC for 1minute
Mechanical performance	Rotational torque				7mN·m max.
	Detent torque	12±5mN·m		40±20mN·m	8±5mN·m
	Push-pull strength	100N			
Environmental performance	Cold	-40±2°C for 240h		-40±3°C for 240h	-30±3°C for 240h
	Dry heat	85±2°C for 240h		85±3°C for 240h	80±3°C for 240h
	Damp heat	60±2°C, 90 to 95% RH for 240h		60±3°C, 90 to 95%RH for 240h	40±2°C, 90 to 95%RH for 240h
Page		204	210	213	215

Push-on Switch Specifications

Items	EC11K/EC11J		EC20A	EM20B
Contact arrangement	Single pole and single throw (Push-on)			
Travel (mm)	0.5±0.3	1.5±0.5		0.5 ^{+0.4} _{-0.3}
Operating force (N)	5±2	4±2		6±3
Rating	0.1A 5V DC		0.5A 16V DC (1mA 16V DC min. ratings)	0.1A 5V DC
Contact resistance	100mΩ for initial period; 200mΩ after operating life			
Operating life	1,000,000 times min.	100,000 times min.	20,000times min.	25,000times min.

Note

○marks in "Available for automotive use" indicate that some of the series products can work at the operating temperature range from -40°C to +85°C.

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
ProductsMetal
ShaftInsulated
ShaftHollow
ShaftRing
Type


Product Varieties

Shaft Dimensions

1. Single-shaft Type

1) Knurled Type

Unit:mm


Configuration(Shaft diameter: $\phi 6$)

Detailed dimensions

L ₁	L ₂	ℓ_1	S ₁
15	5	6	7
20	10	6	7

2) Flat Type

Unit:mm


Configuration(Shaft diameter: $\phi 5.975$)

Detailed dimensions

L ₁	L ₂	ℓ
15	7	5
20	10	7

3) Slotted Type

Unit:mm

Configuration(Shaft diameter: $\phi 5.975$)

Detailed dimensions

L ₁	L ₂
15	7
20	10


Notes

- The highlighted figures in shaft types refer to Product Specifications in P.215.
- Products other than those listed in the above chart are also available. Please contact us for details

Soldering Conditions

Example of Reflow Soldering Condition

- Heating method: Double heating method with infrared heater.
- Temperature measurement: Thermocouple 0.1 to 0.2 ϕ CA (K) or CC (T) at soldering portion (copper foil surface). A heat resisting tape should be used for fixed measurement.
- Temperature profile



Series (Reflow type)	A (°C) 3s max.	B (°C)	C (°C)	D (°C)	E (s)	F (s)	G (s)
EC11J	260	230	180	150	120	—	240

Notes

- The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.
- Soldering conditions differ depending on reflow soldering machines. You are requested to verify the soldering conditions thoroughly beforehand.