


MODEL 78

1-1/4" Rectangular

Multiturn

Cermet Trimming

Potentiometer



ELECTRICAL

Standard Resistance Range, Ohms	10 to 2Meg
Standard Resistance Tolerance	$\pm 10\%$ (<100 Ohms = $\pm 20\%$)
Input Voltage, Maximum	300 Vdc or rms not to exceed power rating
Slider Current, Maximum	100mA or within rated power, whichever is less
Power Rating, Watts	1.0 at 70°C derating to 0 at 125°C
End Resistance, Maximum	2 Ohms
Actual Electrical Travel, Turns, Nominal	22
Dielectric Strength	500 Vrms
Insulation Resistance, Minimum	1,000 Megohms
Resolution	Essentially infinite
Contact Resistance Variation, Maximum	1% or 1 Ohm, whichever is greater

ENVIRONMENTAL

Seal	85°C Fluorinert® (No Leaks)
Temperature Coefficient, Maximum	$\pm 100\text{ppm}/^\circ\text{C}$
Operating Temperature Range	-55°C to +125°C
Thermal Shock	5 cycles, -55°C to +125°C (1% Δ RT, 1% Δ VR)
Moisture Resistance	Ten 24 hour cycles (1% Δ RT, IR 1,000 Megohms Min.)
Shock, 6ms Sawtooth	100G's (1% Δ RT, 1% Δ VR)
Vibration	20G's, 10 to 2,000 Hz (1% Δ RT, 1% Δ VR)
High Temperature Exposure	250 hours at 125°C (2% Δ RT, 2% Δ VR)
Rotational Life	200 cycles (3% Δ RT)
Load Life at 0.5 Watts	1,000 hours at 70°C (2% Δ RT)
Resistance to Solder Heat	260°C for 10 sec. (1% Δ RT)


MECHANICAL

Mechanical Stops	Clutch Action, both ends
Torque, Starting Maximum	5oz.-in. (0.035 N-m)
Weight, Nominal	.09 oz. (2.6 grams)

Fluorinert® is a registered trademark of 3M Company.
Specifications subject to change without notice.


SIDE ADJUSTMENT (Inch/mm)

Model 78P




Note: Model 78P dimensions applicable to all other models except as noted

Model 78L




Model 78S



PANEL MOUNT ADAPTER (Inch/mm)


1

Model 56BW (Adapter Only)




Use .22/5.613 Dia. Min. Mounting Hole


Lock Washer, Panel Nut, Sealing Washer
& Mounting Screws Provided



Model 78LBW (Adapter Pre-Assembled with Trimmer)



Model 78SBW (Adapter Pre-Assembled with Trimmer)



STANDARD RESISTANCE VALUES, OHMS

10	200	5K	50K	500K
20	500	10K	100K	1Meg
50	1K	20K	200K	2Meg
100	2K	25K	250K	

PACKAGING

Standard:	Boxes			
	Capacity	=	25 Units	

ORDERING INFORMATION

78 P BW R 10K

Model Series

Pin Style


Resistance Value

Resistance Prefix

Optional Panel Mount Adapter

Note: Use '56BW' to order panel mount adapter without trimmer

CIRCUIT DIAGRAM



NOTES

Metric equivalents, based on 1 inch = 25.4mm are rounded to the same number of significant figures as in the original English units and are provided for general information only.

Tolerances unless otherwise specified:
Linear = $\pm .01$ inches (.25mm)
Angular = ± 2 degrees

DIMENSIONS

INCH
mm

THIRD ANGLE PROJECTION