

10 Watts

JCA Series



- Compact 1.0" x 0.8" Metal Package
- Industry Standard Pin Out
- 2:1 Input Range
- Single & Dual Outputs
- Operating Temperature -40 °C to +100 °C
- UL & TUV Approval Pending
- 3 Year Warranty

Specification

Input

Input Voltage Range	• 5 V (4.5-9.0 VDC) • 12 V (9-18 VDC) • 24 V (18-36 VDC) • 48 V (36-75 VDC)
Input Current	• See table
Input Filter	• Pi network
Undervoltage Lockout	• Turn On by 95% of rated input • Turn Off by 85% of rated input
Input Reflected Ripple Current	• 80 mA, 5 V input models, 30 mA all others • 12 μH inductor, 5 Hz to 20 MHz
Input Surge	• 5 V models 10 V for 1 s max, • 12 V models 25 V for 1 s max, • 24 V models 50 V for 1 s max, • 48 V models 100 V for 1 s max

Output

Output Voltage	• See table
Initial Set Accuracy	• $\pm 1\%$ max
Start Up Delay	• 30 ms max
Start Up Rise Time	• 3.5 ms typical
Minimum Load	• No minimum load required
Line Regulation	• $\pm 0.3\%$
Load Regulation	• $\pm 1\%$
Cross Regulation	• $\pm 5\%$ on dual output models with one output at 5% load and other varied from 5% to 100%
Transient Response	• 4% max deviation, recovery to within 1% in $< 500 \mu$s for a 25% load change at 1 A/μs
Ripple & Noise	• 50 mV pk-pk, 20 MHz bandwidth
Overcurrent Protection	• 150% typical, trip and restart (hiccup mode)
Short Circuit Protection	• Continuous with auto recovery
Overvoltage Protection	• 150% typical, Recycle input to reset
Temperature Coefficient	• $\pm 0.05\%/^{\circ}\text{C}$

General

Efficiency	• See table
Isolation	• 1500 VDC Input to Output, basic insulation • 500 VDC Input to Case • 500 VDC Output to Case
Switching Frequency	• 300 kHz typical
Power Density	• 31.25 W/in³
MTBF	• > 950 kHrs to MIL-HDBK-217F at 25 °C, GB

Environmental

Operating Temperature	• -40 °C to +100 °C output power derates from 100% load at +70 °C linearly to 0% load at +100 °C
Case Temperature	• +100 °C max
Storage Temperature	• -55 °C to +125 °C
Cooling	• Convection cooled
Operating Humidity	• Up to 95% RH, non-condensing

EMC & Safety

Emissions	• EN55022, level A conducted (level B with external components, see application note), level B radiated
ESD Immunity	• EN61000-4

Models and Ratings

JCA10 **XP**

Input Voltage ⁽¹⁾	Output Voltage	Output Current	Input Current ⁽²⁾		Efficiency	Model Number
			No Load	Full Load		
4.5-9.0 VDC	3.3 VDC	2.42 A	28 mA	560 mA	69%	JCA1005S03
	5.0 VDC	1.60 A	10 mA	535 mA	73%	JCA1005S05
	12.0 VDC	0.83 A	15 mA	526 mA	74%	JCA1005S12
	15.0 VDC	0.66 A	26 mA	559 mA	74%	JCA1005S15
	±5.0 VDC	±0.80 A	15 mA	502 mA	74%	JCA1005D01
	±12.0 VDC	±0.42 A	19 mA	537 mA	73%	JCA1005D02
	±15.0 VDC	±0.33 A	25 mA	560 mA	70%	JCA1005D03
9-18 VDC	3.3 VDC	2.42 A	55 mA	790 mA	84%	JCA1012S03
	5.0 VDC	1.60 A	50 mA	745 mA	89%	JCA1012S05
	12.0 VDC	0.83 A	45 mA	930 mA	89%	JCA1012S12
	15.0 VDC	0.66 A	45 mA	920 mA	89%	JCA1012S15
	±5.0 VDC	±0.80 A	16 mA	785 mA	84%	JCA1012D01
	±12.0 VDC	±0.42 A	45 mA	942 mA	89%	JCA1012D02
	±15.0 VDC	±0.33 A	50 mA	920 mA	89%	JCA1012D03
18-36 VDC	3.3 VDC	2.42 A	3 mA	112 mA	73%	JCA1024S03
	5.0 VDC	1.60 A	3 mA	107 mA	75%	JCA1024S05
	12.0 VDC	0.83 A	4 mA	109 mA	75%	JCA1024S12
	15.0 VDC	0.66 A	4 mA	111 mA	75%	JCA1024S15
	±5.0 VDC	±0.80 A	18 mA	390 mA	85%	JCA1024D01
	±12.0 VDC	±0.42 A	25 mA	470 mA	89%	JCA1024D02
	±15.0 VDC	±0.33 A	6 mA	115 mA	73%	JCA1024D03
36-75 VDC	3.3 VDC	2.42 A	3 mA	62 mA	71%	JCA1048S03
	5.0 VDC	1.60 A	5 mA	58 mA	70%	JCA1048S05
	12.0 VDC	0.83 A	3 mA	58 mA	70%	JCA1048S12
	15.0 VDC	0.66 A	3 mA	59 mA	72%	JCA1048S15
	±5.0 VDC	±0.80 A	2 mA	56 mA	73%	JCA1048D01
	±12.0 VDC	±0.42 A	3 mA	57 mA	73%	JCA1048D02
	±15.0 VDC	±0.33 A	3 mA	60 mA	70%	JCA1048D03

Notes

1. Nominal input voltage 5, 12, 24 or 48 VDC.
 2. Input current is at nominal input voltage.

3. Efficiency is measured at nominal input and full load at 25 °C.

Mechanical Details

