






NOTES:

1. FOR REPLACEMENT OF PARTS OTHER THAN ITEMISED, TOOL SHOULD BE SENT TO OUR TOOL REPAIR DIVISION TO ENSURE PROPER CERTI-CRIMP RATCHET ADJUSTMENT.
2. TOOL TO BE GAUGED WHEN HANDLES ARE CLOSED BUT NOT UNDER PRESSURE.



ENLARGED VIEWS ON CRIMPS SCALE:-4:1

7	39207	ADJUSTMENT PIN	1
6	300432	PIN	2
5	21045-3	RETAINING RING	4
4	21045-6	RETAINING RING	2
3	300449	PIN	1
8	39366	COLLAR	1
1	39364	SPRING	1
PART NO.			525651

CRIMP SYMBOL	TERMINAL NUMBER		WIRE SIZE	INS. SIZE
	STRIP	L. P.		
A	154718	341002	0.7-2.0MM ²	.094-.126
B	154717	341001	2.5-4.0MM ²	.142-.169

© AMP of GREAT BRITAIN LTD 1977				CUSTOMER COPY REFERENCE ONLY	
MATERIAL AND FINISH				AMP of Great Britain Ltd	
WIRE - RANGE - INSULATION				TYPE	
0.7-4.0MM ²				F	
TOLERANCE EXCEPT AS NOTED				SCALE	
± 0.15% (0.38) ± 1%				1:1	
NAME				DOUBLE ACTION HAND TOOL	
TYPE				TYPE F	