



RECOMMENDED PCB LAYOUT (COMPONENT SIDE VIEW)
 EMPFOHLENER FUER LEITERPLATTE (BESTUECKUNGSSEITE)
 TOL ±0.05 [.002] UNLESS NOTED



RECOMMENDED PANEL
 CUTOUT
 EMPFOHLENER FRONTPLATTEN AUSSCHNITT



NO. IDENT. NR.	LED 2 LEFT	LED 1 RIGHT	LED CODE
133565	BLANK	GREEN	L6
133568	YELLOW	GREEN	L1
133740	GREEN	YELLOW	L2
133741	GREEN	GREEN	L3
133742	YELLOW	YELLOW	L8
133743	ORANGE / GREEN	ORNAGE / GREEN	L9

MATERIALS AND FINISH

HOUSING: GLASS FILLED POLYESTER UL 94 V-O BLACK
 SHIELDING: Cu ALLOY, PLATED WITH 1.0µm [40µin] MIN. Ni
 CONTACTS: 0.35 mm PHOSPHOR BRONZE
 CONTACT FINISH: 0.8 µm Au [30 µin], Sn Pb TERMINALS
 LED LENS: EPOXY

MECHANICAL CHARACTERISTICS

DURABILITY: 1000 MATING CYCLES

ELECTRICAL CHARACTERISTICS

CURRENT/VOLTAGE: 125 Vac AT 1.5 AMPS MAX
 DIELECTRIC WITHSTAND VOLTAGE: 1000 Vac RMS MIN., 60 Hz
 INSULATION RESISTANCE: 500 MEGAOHMS MIN.
 CONTACT RESISTANCE: 30 MILLOHMS MAX
 OPERATING TEMPERATURE: -40°C +125°C
 LED OPERATING VOLTAGE: 2.0 TYP., 2.5 MAX @ If = 20 mA

Consider protection memo from DN 34

Information:	Tolerances	Scale 2:1		
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	All Dimensions in mm[in]	Designation	
			MOD JACK - MJE LED, 1X1, SHIELDED	
ERNI Components CHESTER, VA U.S.A.		133829		1
		Rev.	Date	Group/Type