

REV.	DATE	BY-CHKD	REVISIONS	PART NUMBER	GRIP RANGE		" A "		" B "		
A	07DEC94	JSS	PRN:64-187 (SEE REC DWG)		MIN.	MAX.	MIN.	MAX.			
B	02FEB95	JSS	PRN:64-187A	64-11-10	1.2	2	10.4	12.7	11.5		
				64-11-20	2	2.8	11.2	13.5	11.9		
				64-11-30	2.8	3.6	11.9	14.2	12		
FOR AN ASSEMBLY WITH A BLACK POLYESTER POWDER COATED CUP, PADDLE AND COVER; CHANGE THE LAST											




FOR AN ASSEMBLY WITH A BLACK POLYESTER POWDER COATED CUP, PADDLE AND COVER; CHANGE THE LAST DIGIT OF THE PART NUMBER TO "2". EXAMPLE: 64-11-12

LATCH, MOUNTING BRACKET AND NUT ARE SHIPPED SEPARATELY, BULK.

AN OPTIONAL METHOD OF PACKAGING IS ONE ASSEMBLY (LATCH, MOUNTING BRACKET AND NUT) PER BAG. IF THIS METHOD IS PREFERRED, ADD "-2" TO THE END OF THE PART NUMBER. EXAMPLE: 64-11-10-2

INSTALLATION INSTRUCTIONS

PREPARE A RECTANGULAR HOLE IN PANEL, AS SHOWN.
INSERT LATCH AND PLACE MOUNTING BRACKET OVER
STUD. SECURE BRACKET WITH THE MOUNTING NUT.



PANEL PREPARATION

MATERIAL AND FINISH

CUP, PADDLE AND COVER: 304 STAINLESS STEEL,
PASSIVATED PLUS SATIN BRUSHED FINISH.
SLIDE: 1010 STEEL, CHROME PLATED.
PIN: 302 STAINLESS STEEL, PASSIVATED.
SPRINGS: 302 STAINLESS STEEL, PASSIVATED.
STUD: 304 STAINLESS STEEL, PASSIVATED.
MOUNTING BRACKET: 302 STAINLESS STEEL, PASSIVATED.
MOUNTING NUT: 304 STAINLESS STEEL, PASSIVATED
WITH A NYLON INSERT.