



Adhesive Transfer Tapes with Adhesive 300LSE

8132LE • 8153LE • 9453LE • 9471LE • 9472LE
9653LE • 9671LE • 9672LE

Technical Data

April, 2013

Product Description

3M™ Adhesive Transfer Tapes with 3M™ Low Surface Energy Acrylic Adhesive 300LSE provides high bond strength to most surfaces, including many low surface energy plastics such as polypropylene and powder coated paints. The acrylic adhesive also provides excellent adhesion to surfaces contaminated lightly with oil typically used with machine parts.

Product Construction

Product Number	Adhesive: (Solvent Free)	Liner:
3M™ Adhesive Transfer Tape 8132LE	2.3 mils (58 microns) 3M High Strength Acrylic Adhesive 300LSE	4.0 mils (100 microns) 58# Polycoated kraft 6.2 mils (157 microns) 83# Polycoated kraft
3M™ Adhesive Transfer Tape 8153LE	3.5 mils (88 microns) 3M High Strength Acrylic Adhesive 300LSE	4.0 mils (100 microns) 58# Polycoated kraft 6.2 mils (157 microns) 83# Polycoated kraft
3M™ Adhesive Transfer Tape 9453LE	3.6 mils (91 microns) 3M High Strength Acrylic Adhesive 300LSE	4.2 mils (107 microns) 58# Polycoated kraft
3M™ Adhesive Transfer Tape 9471LE	2.3 mils (58 microns) 3M High Strength Acrylic Adhesive 300LSE	4.2 mils (107 microns) 58# Polycoated kraft
3M™ Adhesive Transfer Tape 9472LE	5.2 mils (132 microns) 3M High Strength Acrylic Adhesive 300LSE	4.2 mils (107 microns) 58# Polycoated kraft
3M™ Adhesive Transfer Tape 9653LE	3.5 mils (88 microns) 3M High Strength Acrylic Adhesive 300LSE	6.2 mils (157 microns) 83# Polycoated kraft
3M™ Adhesive Transfer Tape 9671LE	2.3 mils (58 microns) 3M High Strength Acrylic Adhesive 300LSE	6.2 mils (157 microns) 83# Polycoated kraft
3M™ Adhesive Transfer Tape 9672LE	5.0 mils (127 microns) 3M High Strength Acrylic Adhesive 300LSE	6.2 mils (157 microns) 83# Polycoated kraft

3M™ Adhesive Transfer Tapes with Adhesive 300LSE

8132LE • 8153LE • 9453LE • 9471LE • 9472LE • 9653LE • 9671LE • 9672LE • 9698LE

Typical Physical Properties and Performance Characteristics

Typical Adhesion Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Peel Adhesion - ounces/inch (Newtons/100 mm) ASTM D3330, modified: 90° peel, 2 mil aluminum backing.

Typical Adhesion Chart

	3M™ Adhesive Transfer Tape	15 Minute Room Temperature Oz./In. N/100 mm		72 Hour Room Temperature Oz./In. N/100 mm	
Stainless Steel	8132LE 8153LE	71 90	78 98	75 100	82 109
ABS	8132LE 8153LE	70 80	77 88	79 113	86 124
Polypropylene	8132LE 8153LE	69 89	75 97	74 103	81 113
Stainless Steel	9453LE 9471LE 9472LE	90 71 109	98 78 119	100 75 140	109 82 153
ABS	9453LE 9471LE 9472LE	80 70 102	88 77 112	113 79 128	124 86 140
Polypropylene	9453LE 9471LE 9472LE	89 69 115	97 75 126	103 74 136	113 81 149
Stainless Steel	9653LE 9671LE 9672LE	90 71 109	98 78 119	100 75 140	109 82 153
ABS	9653LE 9671LE 9672LE	80 70 102	88 77 112	113 79 128	124 86 140
Polypropylene	9653LE 9671LE 9672LE	89 69 115	97 75 126	103 74 136	113 81 149

3M™ Adhesive Transfer Tapes with Adhesive 300LSE

8132LE • 8153LE • 9453LE • 9471LE • 9472LE • 9653LE • 9671LE • 9672LE

Typical Physical Properties and Performance Characteristics (*continued*)

Typical Adhesion Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

The properties defined are based on the attachment of impervious faceplate materials (such as aluminum) to a stainless steel test surface.

Bond Build-up: The bond strength of 3M™ Adhesive 300LSE increased as a function of time and temperature, and has very high initial adhesion.

Humidity Resistance: High humidity has a minimal effect on adhesive performance. No significant reduction in bond strength is observed after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

U.V. sistance: When properly applied, nameplates and decorative trim parts are not adversely affected by exposure.

Water Resistance: Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

Temperature Cycling Resistance: High bond strength is maintained after cycling four times through:

4 hours at 158°F (70°C)

4 hours at -20°F (-29°C)

4 hours at 73°F (22°C)

Chemical Resistance: When properly applied, nameplates and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids and alkalis.

Temperature Resistance: 3M™ Adhesive 300LSE is usable for short periods (minutes, hours) at temperatures up to 300°F (148°C) and for intermittent longer periods of time (days, weeks) up to 200°F (93°C).

Lower Service Temperature: -40°F (-40°C).

Available Sizes

Width and Length (subject to minimum order requirements):

	3M™ Adhesive Transfer Tapes 8132LE, 8153LE*	3M™ Adhesive Transfer Tapes 9453LE, 9471LE, 9472LE, 9653LE, 9671LE, 9672LE
Standard Sheet Size:	24 in. x 36 in.	—
Limitations:	Maximum 360 yards	1/2 in. to 63/64 in.: Maximum 180 yards 1 in. to 54 in.: Maximum 360 yards
Minimum Slit Width:	12 in.	1/2 in.
Maximum Slit Width:	48 in.	54 in.
Normal Slitting Tolerance:	± 1/32 in.	± 1/32 in.
Core	6.0 in.	3.0 in.

*Custom sheets are available.

3M™ Adhesive Transfer Tapes with Adhesive 300LSE

8132LE • 8153LE • 9453LE • 9471LE • 9472LE • 9653LE • 9671LE • 9672LE • 9698LE

Features

- 3M™ Adhesive 300LSE is a hi-strength acrylic adhesive that provides a very high bond strength to most surfaces.
- Excellent bond to low surface energy plastics such as, polypropylene and powder coatings.
- Excellent adhesion to lightly oiled surfaces typical of machine parts.
- Thickness range of 2.0 mils, 3.5 mils, 5.0 mils and 8.5 mils for use on smooth, or rough surfaces.
- Extremely smooth adhesive for excellent graphics appearance.
- Double lined for selective die-cutting.
- Polycoated kraft liner for die-cutting end tabs and waste removed nameplates on a common carrier.
- 3M™ Adhesive Transfer Tapes 8132LE and 8153LE are double lined for selective die-cutting.

Application Techniques

For maximum bond strength, the surface should be thoroughly cleaned and dried. Typical cleaning solvents are heptane or isopropyl alcohol. Carefully read and follow manufacturer's precautions and directions for use when using cleaning solvents.

Bond strength can also be improved with firm application pressure and moderate heat, from 100°F (38°C) to 130°F (54°C), causing the adhesive to develop intimate contact with the bonding surface.

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended for most pressure-sensitive adhesives because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

General Information

- Plastic nameplates or graphic overlays for use on low surface energy plastics.
- Waste removed nameplates on a common sheet for ease of application.
- Attaching membrane switch assemblies to powder coated surfaces and low surface energy plastics.
- Graphic overlays with end tabs for easy liner removal.
- Graphic application to surfaces such as wood, fabric, plastic, where very high bond strength is required.
- Attaching identification material to lightly oily surfaces typical of machine parts.

Application Ideas

Processing:

Slitting and die-cutting: This adhesive is very aggressive and may be difficult to convert depending on your application requirements. Chilling the adhesive between 35°F and 50°F will improve the processability. In addition, dies can be lubricated with Laminoleum evaporative stamping oil, which is available from Metal Lubricants Company (708-333-8900), or with Lubri-Blade 907 from Ceramic Technologies Inc. (800-258-8495). You may also refer to our Technical Bulletin on 3M™ Adhesive 300LSE converting. (70-0707-6205-2)

Roll Laminating: A combination of metal and rubber rollers with moderate pressure is recommended.

Note: Please refer to the Technical Bulletin on slitting. (70-0709-3905-6)

3M™ Adhesive Transfer Tapes with Adhesive 300LSE

8132LE • 8153LE • 9453LE • 9471LE • 9472LE • 9653LE • 9671LE • 9672LE

Storage	Store at room temperature conditions of 70°F (21°C) and 50% relative humidity.
Shelf Life	If stored properly, product retains its performance and properties for 18 months from date of shipment.
Recognition/ Certification	TSCA: These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements. MSDS: These products are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the products should not present a health and safety hazard. However, use or processing of the products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards. Note: One of 3M's core values is to respect our social and physical environment. 3M is committed to comply with ever-changing, global, regulatory and consumer environmental, health, and safety (EHS) requirements. As a service to our customers, 3M is providing information on the regulatory status of many 3M products. Further regulation information including that for OSHA, USCPSP, FDA, California Proposition 65, REACH and RoHS, can be found at 3M.com/regs.
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes Division Converter Markets

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-223-7427 • 651-778-4244 (fax)
www.3M.com/converter



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2013 70070937951 (4/13)