


8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.			
PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION	
1852141-1		A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER	
1852141-2		A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER	
1852141-3		A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER	
1852141-6		A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER	
7-1852141-7		A	-	-	-	SPARE PARTS	

- △ RECOMMENDED SPARE PARTS
△ GREASE LIGHTLY
△ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE




TERMINAL NAME: TERMINAL, PIN					
AMP PART NO.	COMP TERM NO.	YAZAKI TERMINAL - AMP CRIMP SPECS			
1572824	7114-4729-02				
-	-	PAD LTR	CRIMP HEIGHT	WIRE SIZE	
-	-	A	.041±.002[1.04±0.05mm]	20 AWG	
-	-	B	.036±.002[.91±0.05mm]	22 AWG	
-	-	C	-	-	
-	-	D	-	-	
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	.055 [1.40mm]	F	22-20 AWG
-	-	INSUL	.062 [1.57mm]	O	-
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPL INSTRUCTIONS	SET UP GAGE	
.143 - .158	NONE	.320	408-8040	458637-1	

LOC		DIST		REVISONS			
A	66	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		RELEASED	31OCT2005	LG	TE

-	2	2	2	2	-	5-354779-0	PIN, WIRE DISC, .3240	127
-	2	2	2	2	-	4-354779-0	PIN, WIRE DISC, .3190	126
-	-	-	REF	-	-	455749-1	GUARD WINDOW	116
-	-	REF	-	-	-	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	53
-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	690753-1	SPACER, TONKER	50
-	-	-	-	-	-	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	-	-	-	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	-	-	690501-4	CAM, POST FEED, 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
-	1	1	1	1	-	690191-1	PLUG,NYLON	45
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	690124-1	WASHER, RAM (.115)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	690142-1	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-3	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1320908-4	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-1	SUB-ASSEMBLY, FEEDTRACK	29
-	1	1	1	1	-	1320928-3	PLATE, STRIP GUIDE	24
-	1	-	-	-	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	-	-	-	691353-1	STRIPPER	19
-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	17
-	1	1	1	1	-	5-22280-0	SPRING, COMPRESSION	12
-	1	1	1	1	-	690461-1	STOP, SHEAR	11
-	-	1	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
-	1	1	1	1	-	462006-1	FLOATING SHEAR, FRONT	9
1	1	1	1	1	-	2-1633117-5	ANVIL, COMBINATION	8
-	1	1	1	1	-	5-240641-9	SPACER	7
-	1	1	1	1	-	2-455889-0	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	3-238011-8	BLOCK, CRIMPER SPACER	4
1	1	1	1	1	-	5-1583690-0	CRIMPER, INSUL O	3
1	1	1	1	1	-	1-456402-4	CRIMPER, WIRE PREMIUM	1

-77		-6	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO
THIS IS A CUSTOMER DRAWING. THE CUSTOMER IS RESPONSIBLE FOR THE CORRECTNESS OF THE INFORMATION PROVIDED. THE CUSTOMER SHALL BE RESPONSIBLE FOR THE CORRECTNESS OF THE INFORMATION PROVIDED.							DWN B. HIGMAN 14OCT2005	tyco Electronics	Tyco Electronics Harrisburg, PA 17105-3608
DIMENSIONS: INCHES							CHK B. HIGMAN 14OCT2005	NAME	SIDE FEED HDM APPLICATOR
TOLERANCES UNLESS OTHERWISE SPECIFIED:							APVD T. ELBIN 14OCT2005	PRODUCT SPEC	-
1 PLC ±.01 2 PLC ±.01 3 PLC ±.01 4 PLC ±.0001							APPLICATION SPEC	-	-
MATERIAL							FINISH	WEIGHT	-
CUSTOMER DRAWING							SCALE	3:5	SHEET 1 OF 1
CUSTOMER VIEWABLE ASSEMBLY							REV	A	-



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852141-3](#)