


# EMK13H2H-35.805M



**ECLIPTEK**  
CORPORATION



## ELECTRICAL SPECIFICATIONS


|                                 |  |
|---------------------------------|--|
| Nominal Frequency               | 35.805MHz  |
| Frequency Tolerance/Stability   | ±50ppm Maximum over -40°C to +85°C (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, 260°C Reflow, Shock, and Vibration) |
| Aging at 25°C                   | ±1ppm Maximum First Year   |
| Operating Temperature Range     | -40°C to +85°C   |
| Supply Voltage                  | 3.3Vdc ±10%  |
| Input Current                   | 25mA Maximum   |
| Output Voltage Logic High (Voh) | 90% of Vdd Minimum (IOH=-8mA)  |
| Output Voltage Logic Low (Vol)  | 10% of Vdd Maximum (IOL=+8mA)  |
| Rise/Fall Time                  | 2nSec Maximum (Measured from 20% to 80% of waveform)   |
| Duty Cycle                      | 50 ±5(%) (Measured at 50% of waveform)   |
| Load Drive Capability           | 15pF Maximum   |
| Output Logic Type               | CMOS   |
| Output Control Function         | Tri-State (Disabled Output: High Impedance)  |
| Output Control Input Voltage    | +0.7Vdd Minimum or No Connect to Enable Output, +0.3Vdd Maximum to Disable Output  |
| Peak to Peak Jitter (tPK)       | 250pSec Maximum, 100pSec Typical   |
| Start Up Time                   | 50mSec Maximum   |
| Storage Temperature Range       | -55°C to +125°C  |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |  |
|------------------------------|--|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 2, HBM 2000V                       |
| Flammability                 | UL94-V0  |
| Mechanical Shock             | MIL-STD-883, Method 2002, Condition G, 30,000G                     |
| Moisture Resistance          | MIL-STD-883, Method 1004   |
| Moisture Sensitivity Level   | J-STD-020, MSL 1   |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K                               |
| Resistance to Solvents       | MIL-STD-202, Method 215  |
| Solderability                | MIL-STD-883, Method 2003 (Four I/O Pads on bottom of package only) |
| Temperature Cycling          | MIL-STD-883, Method 1010, Condition B                              |
| Thermal Shock                | MIL-STD-883, Method 1011, Condition B                              |
| Vibration                    | MIL-STD-883, Method 2007, Condition A, 20G                         |

# EMK13H2H-35.805M

## MECHANICAL DIMENSIONS (all dimensions in millimeters)



| PIN | CONNECTION                 |
|-----|----------------------------|
| 1   | Tri-State (High Impedance) |
| 1   | Power Down (Logic Low)     |
| 2   | Ground                     |
| 3   | Output                     |
| 4   | Supply Voltage             |


  

| LINE | MARKING   |
|------|---|
| 1    | XXXX<br>XXXX=Ecliptek<br>Manufacturing Lot Code |

Note A: Center paddle is connected internally to oscillator ground (Pad 2).


## Suggested Solder Pad Layout

All Dimensions in Millimeters




All Tolerances are  $\pm 0.1$

## OUTPUT WAVEFORM & TIMING DIAGRAM



## Test Circuit for CMOS Output




Note 1: An external  $0.1\mu F$  low frequency tantalum bypass capacitor in parallel with a  $0.01\mu F$  high frequency ceramic bypass capacitor close to the package ground and  $V_{DD}$  pin is required.

Note 2: A low capacitance ( $<12pF$ ), 10X attenuation factor, high impedance ( $>10Mohms$ ), and high bandwidth ( $>300MHz$ ) passive probe is recommended.

Note 3: Capacitance value  $C_L$  includes sum of all probe and fixture capacitance.


## Recommended Solder Reflow Methods



### High Temperature Infrared/Convection

|  |                                      |
|--|--------------------------------------|
| $T_s \text{ MAX to } T_l$ (Ramp-up Rate)                   | 3°C/second Maximum                   |
| <b>Preheat</b>   |                                      |
| - Temperature Minimum ( $T_s \text{ MIN}$ )                | 150°C                                |
| - Temperature Typical ( $T_s \text{ TYP}$ )                | 175°C                                |
| - Temperature Maximum ( $T_s \text{ MAX}$ )                | 200°C                                |
| - Time ( $t_s \text{ MIN}$ )                               | 60 - 180 Seconds                     |
| <b>Ramp-up Rate (<math>T_l</math> to <math>T_p</math>)</b> | 3°C/second Maximum                   |
| <b>Time Maintained Above:</b>                              |                                      |
| - Temperature ( $T_l$ )                                    | 217°C                                |
| - Time ( $t_l$ )   | 60 - 150 Seconds                     |
| <b>Peak Temperature (<math>T_p</math>)</b>                 | 260°C Maximum for 10 Seconds Maximum |
| <b>Target Peak Temperature (<math>T_p</math> Target)</b>   | 250°C $+0/-5^\circ\text{C}$          |
| <b>Time within 5°C of actual peak (<math>t_p</math>)</b>   | 20 - 40 seconds                      |
| <b>Ramp-down Rate</b>                                      | 6°C/second Maximum                   |
| <b>Time 25°C to Peak Temperature (t)</b>                   | 8 minutes Maximum                    |
| <b>Moisture Sensitivity Level</b>                          | Level 1                              |

## Recommended Solder Reflow Methods



### Low Temperature Infrared/Convection 240°C

**$T_s \text{ MAX to } T_L$  (Ramp-up Rate)** 5°C/second Maximum

#### Preheat

|   |                  |
|---|------------------|
| - Temperature Minimum ( $T_s \text{ MIN}$ ) | N/A              |
| - Temperature Typical ( $T_s \text{ TYP}$ ) | 150°C            |
| - Temperature Maximum ( $T_s \text{ MAX}$ ) | N/A              |
| - Time ( $t_s \text{ MIN}$ )                | 60 - 120 Seconds |

**Ramp-up Rate ( $T_L$  to  $T_p$ )** 5°C/second Maximum

#### Time Maintained Above:

|                         |                     |
|-------------------------|---------------------|
| - Temperature ( $T_L$ ) | 150°C               |
| - Time ( $t_L$ )        | 200 Seconds Maximum |

**Peak Temperature ( $T_p$ )** 240°C Maximum

**Target Peak Temperature ( $T_p \text{ Target}$ )** 240°C Maximum 1 Time / 230°C Maximum 2 Times

**Time within 5°C of actual peak ( $t_p$ )** 10 seconds Maximum 2 Times / 80 seconds Maximum 1 Time

**Ramp-down Rate** 5°C/second Maximum

**Time 25°C to Peak Temperature (t)** N/A

**Moisture Sensitivity Level** Level 1

### Low Temperature Manual Soldering

185°C Maximum for 10 seconds Maximum, 2 times Maximum.

### High Temperature Manual Soldering

260°C Maximum for 5 seconds Maximum, 2 times Maximum.