



222A132-100-0 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Molded Parts

222A132-100-0

222A132-100-0

TE Internal Number: 665862-000

Product Highlights [View All](#)

- BR1326 listed Class G, BS-G-198-5-DF, DEF Std 59-97 Issue 3 Type DF, IEC 62329-3-101
- Molded Part Type = Molded Boot
- Connector or Backshell Outside Diameter = 16.00 mm, 18.00 mm, 20.00 mm
- Wire/Cable Outside Diameter = 7.00 mm, 8.00 mm, 9.00 mm, 10.00 mm, 11.00 mm, 12.00 mm
- Molded Part Shape = 90°

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[\[+\] Feedback](#)
[Documents](#) | **Features** | [Compliance](#)
Please Note:
 Use the Product Drawing for all design activity

Product Type Features

Molded Part Type	Molded Boot
Molded Part Shape	90°
Molded Part Lip	Without Lip
Angle	90°
Adhesive Description	Adhesive Purchased Separately
Size	32
Family Name	222A1

Configuration Features

Material Code	100
---------------	-----

Industry Standards

Government/Industry Qualification	No
Approved Standards	BR1326 listed Class G, BS-G-198-5-DF, DEF Std 59-97 Issue 3 Type DF, IEC 62329-3-101
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)
[View Part in Product Feature Selector](#)
[Check for Tooling](#)

Mechanical Attachment

Adhesive Pre-Coating	Without
----------------------	---------

Dimensions

Connector or Backshell Outside Diameter (mm [in])	16.00 [0.630], 18.00 [0.709], 20.00 [0.787]
Wire/Cable Outside Diameter (mm [in])	7.00 [0.276], 8.00 [0.310], 9.00 [0.350], 10.00 [0.390], 11.00 [0.430], 12.00 [0.470]
Cable Diameter Range (mm [in])	6.40 – 20.60 [0.252 – 0.811]

Body Features

Material	Low Fire Hazard Material
----------	--------------------------

Housing Features

Material Systems Code	100
-----------------------	-----

Environmental

Operating Temperature (°C)	-30 – +105
----------------------------	------------

Operation/Application

Application	Marine, Rail, Military
-------------	------------------------

Purchasing Information

Adhesive Code	S1006, S1030, S1125
---------------	---------------------

Other

Adhesive Options	S1030 Separate Adhesive, -80°C to +80°C (-112°F to +176°F), S1048 Separate Adhesive, -55°C to +105°C (-67°F to +221°F), S1125 Separate Adhesive, -75°C to +150°C (-103°F to +302°F)
Brand	Raychem
Comment	Contact Raychem for additional adhesive and/or cut off boot length information

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

