












T3-1/4 (9mm) Miniature Based LED Lamps

Miniature Packages	Replaces Incandescent	Part Number	Electrical-Optical Characteristics (Ta = 25°C)			Angle of Illumination	Special Features
			Voltage V typ	Current mA typ	Intensity mcd		
470nm Super Blue SiC/GaN  BF321 	6MB, 44, 47, 755	BF321-0PB-006B	5/6V	15	116	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF321 With B321 for Std. Beam (15°)
	12MB, 756	BF321-0PB-014B	12/14V	15	116		
	24MB,	BF321-0PB-024B	24V	15	116		
	313,757,1819,1829	BF321-0PB-028B	28V	15	116		
	48MB	BF321-0PB-048B	48V	12	84		
	60MB,1835	BF321-0PB-060B	60V	12	84		
	120MB, NE51H	BF321-0PB-120A	120VAC	10	74		
470nm Super Blue SiC/GaN  BF304 	6MB, 44, 47, 755	BF304-0PB-006B	5/6V	60	464	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF304 With B304 for Std. Beam (15°)
	12MB, 756	BF304-0PB-014B	12/14V	30	464		
	24MB,	BF304-0PB-024B	24V	15	464		
	313,757,1819,1829	BF304-0PB-028B	28V	15	464		
	48MB	BF304-0PB-048B	48V	12	336		
	60MB,1835	BF304-0PB-060B	60V	12	336		
	120MB, NE51H	BF304-0PB-120A	120VAC	10	296		
470nm Super Blue SiC/GaN  BF3126/ BF3127 	6MB, 44, 47, 755	BF3126-0PB-006B	5/6V	90	360	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF3126/3127 With B3126/3127 for Std. Beam (15°)
	12MB, 756	BF3126-0PB-014B	12/14V	30	360		
	24MB,	BF3127-0PB-024B	24V	15	420		
	313,757,1819,1829	BF3127-0PB-028B	28V	15	420		
	48MB	BF3127-0PB-048B	48V	12	336		
	60MB,1835	BF3127-0PB-060B	60V	12	336		
	120MB, NE51H	BF3127-0PB-120A	120VAC	10	315		
		BF3127-0PB-130B	130V	8	252		

Options

All dimensions in inches. For millimeters multiply by 25.4



Log # 122L Rev 10-2000