

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED

LOC

LOC

DIST

DIST

REVISIONS

P

LTR

DESCRIPTION

DA

DWN

APV

5

RD/CS





D. RE

FCB 13 008501

1350

KH

TN



1.484	37.69	14	4-644894-4
1.384	35.15	13	4-644894-3
1.284	32.61	12	4-644894-2
1.184	30.07	11	4-644894-1
1.084	27.53	10	4-644894-0
.984	24.99	9	3-644894-9
.884	22.45	8	3-644894-8
.784	19.91	7	3-644894-7
.684	17.37	6	3-644894-6
.584	14.83	5	3-644894-5
.484	12.29	4	3-644894-4
.384	9.75	3	3-644894-3
.284	7.21	2	3-644894-2

1.484	37.69	14	1-644894-4
1.384	35.15	13	1-644894-3
1.284	32.61	12	1-644894-2
1.184	30.07	11	1-644894-1
1.084	27.53	10	1-644894-0
.984	24.99	9	644894-9
.884	22.45	8	644894-8
.784	19.91	7	644894-7
.684	17.37	6	644894-6
.584	14.83	5	644894-5
.484	12.29	4	644894-4
.384	9.75	3	644894-3
.284	7.21	2	644894-2

IN	MM	NO OF POSITIONS	PART NUMBER
L		HEADER ASSEMBLY	

25/JUNE/2005			TE Connectivity	
25/JUNE/2005				
25/JUNE/2005	NAME			
CST-100 SHROUDED HEADER ASSEMBLY, FRICTION LOCK, RIGHT ANGLE POST, TIN OR TIN LEAD PLATED				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A1	00779	C-644894	—	
DRAWING		SCALE	SHEET	OF
		10:1	1	REV C

.030	0.76	.107	2.72	—	—
.025	0.64	.100	2.54	—	—
.010	0.25	.092	2.34	.410	10.41
.005	0.13	.063	1.60	.313	7.95
.001	0.03	.040	1.02	.300	7.62
.000350	0.0089	.036	0.91	.280	7.11
.000150	0.00381	.035	0.89	.176	4.47
.000	0.00	.032	0.81	.130	3.30
IN	MM	IN	MM	IN	MM

CONVERSION TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN K. WHITAKER 25JUNE2005 GRK D. BOSSI 25JUNE2005		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME CST-100 SHROUDED HEADER ASSEMBLY, FRICTION LOCK, RIGHT ANGLE POST, TIN OR TIN LEAD PLATED	
		APVD D. BOSSI 25JUNE2005 PRODUCT SPEC — APPLICATION SPEC —		SIZE A1	
MATERIAL 		FINISH 		CODE 00779	
		WEIGHT —		DRAWING NO C-644894	
CUSTOMER DRAWING				SCALE 10:1 SHEET 1 OF 1 REV C	