

AC Line Rated Ceramic Disc Capacitors Class X1, 275 V_{AC}



FEATURES

- Complying with IEC 60384-14 3rd edition
- High reliability
- Wide range of different leadstyles
- Singlelayer AC Disc safety capacitors
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS

- X1 according to IEC 60384-14.3
- EMI filters

DESIGN

The capacitors consist of ceramic disc both sides of which are silver plated. Connection leads are made of tinned copper having diameters of 0.6 mm.

The capacitors may be supplied with straight or kinked leads having a lead spacing of 7.5 mm.

Coating is made of blue colored flame retardant epoxy resin in accordance with UL 94 V-0.

CAPACITANCE RANGE

4.7 nF to 22 nF

TOLERANCE ON CAPACITANCE

± 20 %

RATED VOLTAGE

X1: 275 V_{AC}, 50 Hz (IEC 60384-14.3)
275 V_{AC}, 50 Hz/60 Hz (US/UL/CSA 60384-14)

TEST VOLTAGE

- 4000 V_{DC}, 2 s Component test (100 %)
- 3500 V_{DC}, 60 s Random sampling test (destructive)
- 2000 V_{AC}, 50 Hz, 60 s Voltage proof of coating (destructive)

INSULATION RESISTANCE AT 500 V_{DC}

≥ 6000 MΩ (60 s)

DISSIPATION FACTOR

Class 2: max. 2.5 % (1 kHz)

QUICK REFERENCE DATA

DESCRIPTION	VALUE
Ceramic Class	2
Ceramic Dielectric	Y5V
Voltage (V _{AC})	275
Min. Capacitance (pF)	4700
Max. Capacitance (pF)	22 000
Mounting	Radial

MARKING

Marking indicates series, AC rating, capacitance, tolerance code, and approvals.

OPERATING TEMPERATURE RANGE

-40 °C to +125 °C

TEMPERATURE CHARACTERISTICS

Class 2 Y5V


SECTIONAL SPECIFICATIONS

Climatic category (according to EN 60058-1)

Class 2 40/125/21

APPROVALS

IEC 60384-14.3


DIMENSIONS in millimeters

TECHNICAL DATA

CAPACITANCE C (pF)	CAPACITANCE TOLERANCE	BODY DIAMETER D _{MAX.} (mm)	BODY THICKNESS S _{MAX.} (mm)	LEAD SPACING ⁽¹⁾ F (mm) ± 1 mm	LEAD DIAMETER ⁽¹⁾ d (mm) ± 0.05 mm	WIDTH ⁽¹⁾ V (mm) ± 0.5 mm	PART NUMBER MISSING DIGITS SEE ORDERING CODE BELOW
Y5V (2F3)							
4700	± 20 %	11.0	3.0	7.5	0.6	1.4	W1X472#CV###KR
6800		11.0					W1X682#CV###KR
10 000		15.0					W1X103#CV###KR
15 000	-20 %/+50 %	17.0				1.6	W1X153#CV###KR
22 000		20.0					W1X223#CV###KR

Note
⁽¹⁾ Standard lead configuration, other lead spacing and diameter available on request

ORDERING CODE

#	7 th digit	Capacitance tolerance		± 10 % = K, ± 20 % = M			
###	10 th to 12 th digit	Lead configuration		see “General Information”			
Example	W1X	223	M	CV	CRU	K	R
	Series	Capacitance value	Tolerance code	Voltage code	Lead configuration	Internal code	RoHS compliant

MARKING




APPROVALS

IEC 60384-14.3 - Safety tests

This approval together with CB test certificate substitutes all national approvals.

CB Certificate

X1-capacitor: CB test certificate:

DE 1-11148-A1

4.7 nF to 22 nF

275 V_{AC}



Minimum thickness of insulation: 0.4 mm

VDE

X1-capacitor: VDE marks approval:

137890

4.7 nF to 22 nF


275 V_{AC}




DIN EN 60384-14 VDE 0565-1-1:2006-04 - Safety tests

Minimum thickness of insulation: 0.4 mm

LEAKAGE CURRENT VS. VOLTAGE (typical)



IMPEDANCE VS. FREQUENCY (typical)



RELATED DOCUMENTS

General Information	www.vishay.com/doc?22001
CB Test Certificate	www.vishay.com/doc?22223
VDE Marks Approval	www.vishay.com/doc?22224



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.