



### Part Number: 120102-0013

PROFIBUS\* Straight D-Sub to Dual D-Sub, Straight to 90° 1.0m Cable Length, PUR Cable



Series image - Reference only

<b>Status:</b>	<b>OBSOLETE</b>
<b>Replacement:</b>	Contact Molex
<b>Series:</b>	<u>120102</u>
<b>Category:</b>	Industrial Cordsets
<b>Overview:</b>	<u>Brad® PROFIBUS Solutions</u>
<b>Old Part Number:</b>	@MM3G62PP4M010

### Product Environmental Compliance

EU RoHS: Compliance Status Not Reviewed

China RoHS:

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

### Part Detail

#### General

<b>Status</b>	<b>Obsolete</b>
Category	Industrial Cordsets
Series	<u>120102</u>
Connector End A	D-Sub (9-pin)
Connector End B	Dual D-Sub (9-pin)
IP Rating	IP40
NEMA Rating	NEMA 4
Overview	<u>Brad® PROFIBUS Solutions</u>
Product Name	Profibus*
Type	Double Ended
UPC	78678809031

#### Physical

Cable Diameter	8.00mm (.315")
Cable Length	1.0m
Color - Cable Jacket	Purple
Coupling Style	Threaded
Gender	Male-Male
Keyway	Reverse
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	ABS
Material - Contact	N/A
Material - Coupling Nut	Gray Anodized Aluminum
Material - Plating Mating	N/A
Net Weight	453.540/kg
Orientation	Straight to 90°
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	22
Wire/Cable Type	N/A

#### Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	4A
Voltage - Maximum	30V AC/DC

#### Material Info

Old Part Number	@MM3G62PP4M010
-----------------	----------------

#### Reference - Drawing Numbers

Sales Drawing	SD-120102-002
---------------	---------------

### Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

### Previously Available Application

#### Tooling

[Check our list of old tooling that used to be available for this part](#)