




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G1	REVISED PER ECO-09-021826	6JAN10	KK	AEG

- | | |
|---|--|
| 1. | ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS |
| 2. | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE
HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD |
|  | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
|  | POINT OF MEASUREMENT FOR PLATING THICKNESS |
|  | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI |



RECOMMENDED HOLE LAYOUT

		3.984	3.900	39	80	4-103240-0
OBSOLETE △5		3.884	3.800	38	78	3-103240-9
		3.784	3.700	37	76	3-103240-8
		3.684	3.600	36	74	3-103240-7
		3.584	3.500	35	72	3-103240-6
		3.484	3.400	34	70	3-103240-5
		3.384	3.300	33	68	3-103240-4
		3.284	3.200	32	66	3-103240-3
		3.184	3.100	31	64	3-103240-2
		3.084	3.000	30	62	3-103240-1
	2.984	2.900	29	60	3-103240-0	
△5	OBSOLETE	2.884	2.800	28	58	2-103240-9
		2.784	2.700	27	56	2-103240-8
△5	OBSOLETE	2.684	2.600	26	54	2-103240-7
		2.584	2.500	25	52	2-103240-6
		2.484	2.400	24	50	2-103240-5
△5	OBSOLETE	2.384	2.300	23	48	2-103240-4
		2.284	2.200	22	46	2-103240-3
		2.184	2.100	21	44	2-103240-2
△5	OBSOLETE	2.084	2.000	20	42	2-103240-1
		1.984	1.900	19	40	2-103240-0
		1.884	1.800	18	38	1-103240-9
△5	OBSOLETE	1.784	1.700	17	36	1-103240-8
		1.684	1.600	16	34	1-103240-7
		1.584	1.500	15	32	1-103240-6
DED BY 6-146257-1		1.484	1.400	14	30	1-103240-5
		1.384	1.300	13	28	1-103240-4
DED BY 6-146257-3		1.284	1.200	12	26	1-103240-3
		1.184	1.100	11	24	1-103240-2
DED BY 6-146257-5		1.084	1.000	10	22	1-103240-1
		.984	.900	9	20	1-103240-0
		.884	.800	8	18	103240-9
		.784	.700	7	16	103240-8
		.684	.600	6	14	103240-7
		.584	.500	5	12	103240-6
		.484	.400	4	10	103240-5
		.384	.300	3	8	103240-4
		.284	.200	2	6	103240-3
		.184	.100	1	4	103240-2
		.084	—	—	2	103240-1
		C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL		130CT87		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T. CLARK		200CT87	
		APVD T. CLARK		200CT87		NAME	
		PRODUCT SPEC		—		HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.100 $\square$ VERTICAL, WITH .025 SQ POSTS	
		APPLICATION SPEC		—			
MATERIAL : HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK		FINISH : POST: .000030 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL ALL OVER .000050 NICKEL		WEIGHT		—	
POST: PHOSPHOR BRONZE		CUSTOMER DRAWING		SIZE		CAGE CODE	
				DRAWING NO		RESTRICTED TO	
				A2 00779		C-103240	
				SCALE		SHEET	
				4 : 1		1 of 1	
						REV	
						G1	