












High-precision female headers soldering technique

for 0.635 mm and up to 0.85 mm Ø

art. no.			
BL 5 ...			
art. no.			
BL 6 ...			
art. no.			
BL KG 3 ...			
art. no.			
BL 7 ...			
please indicate:	... no. of contacts one row 1 - 36 two rows 2 - 72 three rows 9 - 96		
art. no.			
BL 8 ...			
please indicate:	... no. of contacts two rows 4 - 72		

contact shell surface: tin-plated
contact spring: gold-plated
BL 8 ...: packing (option) bar magazine (min. 6 contacts)
No capillary action when soldering due to protected contact insert.
V-notches permit breaking! Therefore any required number of contacts is available.