






P.C.B. LAYOUT



6601-XX(G)-PPS/PBT

PPS=(BROWN)
GOLD PLATE
20,28,32,44,52,68,84
SERIES NO.

MATERIALS:
CONTACT COPPER ALLOY TIN PLATED.
HOUSING (A) RYTON(R-4)PPS COMPOUNDS BROWN
(B) PBT UL94V-0 BLACK
POLYPHENYLENE SULFIDE,UL94V-0
ELECTRICAL CHARACTERISTICS:
CURRENT RATING 1A MIN.
WIRHSTANDING VOLTAGE .. AC 500V R.M.S.
INSULATION RESISTANCE .. 1000M OHM UP.
CONTACT RESISTANCE 30 MILLOHMS MAX
OPERATING TEMPERATURE .. CONTINUOUS -55°C ~ +110°C
GOLD PLATE: 1.5~2.0μ"

CONTACTS	A	B	C	D	E	F	G	H	I	J
20	5.08	15.56	17.06	10.16	9.30	9.30	11.30	8.10	15.56	5.08
28	7.62	18.10	20.70	12.70	11.90	11.90	11.30	8.10	18.10	7.62
32	7.62	18.10	22.80	12.70	11.90	14.00	11.30	8.10	20.64	10.16
44	12.70	23.18	27.80	17.78	16.76	16.76	11.30	8.10	23.18	12.70
52	15.24	25.72	31.50	20.32	19.12	19.12	11.30	8.10	25.72	15.24
68	20.32	30.80	39.00	25.40	25.25	25.25	11.30	8.10	30.80	20.32
84	25.40	35.88	46.15	30.48	29.28	29.28	11.30	8.10	35.88	25.40

				DRAWN: Jerry Chen	GENERAL TOLERANCE: .X=±0.2 .XX=±0.15		DESCRIPTION: PLCC SOCKET	SIZE A4
E				CHECKED:				
D					SCALE:	PART NO: 6601-XX(G)-PPS/PBT		
C					SHEET: 1 / 1			
B				APPROVAL:	PROJECTION:			
A	12-08-1998		Jerry Chen					
REV	DATE	FILE	BY					