


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS					DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	A	Redrawn in Autocad	JAP	11/27/91				
1116	B	Drawing was CBS-DY-****	JWM	6/11/01	JC	6/20/01	JC	6/20/01

NOTES:

1. MATERIAL: ELECTRO-TIN PLATED COPPER WITH NYLON 6/6 SLEEVE
FLAMMABILITY: UL94V-2
2. CONTINUOUS OPERATING TEMPERATURE:
-40°F (-40°C) TO 167°F (75°C)
3. VOLTAGE RATING: 600 V
4. TO BE FREE OF BURRS.



PART NUMBER	WIRE RANGE (AWG)	STUD SIZE	L	W	E	C	S	T	M	U	COLOR
CBS-DY-1006	12 - 10	#6 .138	1.03	.32	.84	.29	.148	.135	.250	.040	YELLOW
CBS-DY-1010	12 - 10	#10 .190	1.03	.32	.84	.29	.200	.135	.250	.040	YELLOW
CBS-DY-1406	16 - 14	#6 .138	.86	.30	.71	.25	.148	.090	.170	.030	BLUE
CBS-DY-1408	16 - 14	#8 .164	.86	.30	.71	.25	.174	.090	.170	.030	BLUE
CBS-DY-1410	16 - 14	#10 .190	.86	.30	.71	.25	.200	.090	.170	.030	BLUE
CBS-DY-1804	22 - 18	#4 .112	.84	.25	.69	.25	.120	.070	.145	.030	RED
CBS-DY-1806	22 - 18	#6 .138	.84	.25	.69	.25	.148	.070	.145	.030	RED
CBS-DY-1808	22 - 18	#8 .164	.84	.30	.69	.25	.174	.070	.145	.030	RED
CBS-DY-1810	22 - 18	#10 .190	.84	.30	.69	.25	.200	.070	.145	.030	RED

LISTED



E38918



LR22190K6

OSHA
Acceptable

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

Tolerances: Unless
Otherwise Specified:

.X = ±.015
.XX = ±.010
.XXX = ±.005

DRAWN BY:

JC

DATE:

3/7/91

CHECKED BY:

JOHN COLE

DATE:

12/2/91

APPROVED BY:

J Lisko

DATE:

12/2/91

DRAWING TITLE:

Nylon Insulated Block Fork Terminals

SIZE

DWG. NO.

TA-351

ELECTRONIC FILE

REV

TA-351.dwg

B

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1



SPC TECHNOLOGY