

LOC	DIST	REVISIONS ÄNDERUNGEN					
		P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
A1	—		B4	REVISED PER ECR-11-025934	28DEC11	RK	HMR
			B4	SEE E-12-000819	13JAN12	HS	RH

D

D

C




C

B

B

A

A



- NOTES
Bemerkungen
- 1

AMP-LOGO OR TE-LOGO
AMP-Logo oder TE-Logo
- 2

ORDER-NUMBER
Bestell-Nummer
- 3


REVISIONS-NUMBER
Werkzeugaenderungsindex
- 4

MATERIAL MARKING
Werkstoffkennzeichnung
- 5

CAVITY MARKING
Nestmarkierung
- 6

PRODUCTION-DATE
Produktions-Datum
- B1

7
DIMENSION DEVIATIONS AT MOLDPARTING LINES,
EJECTOR PINS CAUSED BY BURR ACCEPTABLE
Im Bereich der Formtrennungen, Auswerfer
Maszabweichungen durch Gratbildung
zulaessig



MATED WITH TE-COUNTERPART:
Passend zu TE-Gegenstueck:

INTERFACE DRAWING 114-18063-18
Schnittstellenzeichnung 114-18063-18

-

-

CODING Z SHOWN
Kodierung Z dargestellt

MICRO QUADLOK Buchsenkontakt							—	—	—	—	—	—	—	—	
0-963715-1	0-963729-1	>0.5-0.75	CuNiSi	vorverzinnt	0-878591-2	0-734464-1	—	(A1)	0-1241634-3	B	1	PA66	BLACK	MQS HSG., 4POS., COD.C	3
0-928999-1	0-963726-1	0.2-0.5	CuNiSi	vorverzinnt	0-878439-2	0-734237-2	—	(A1)	0-1241634-2	B	1	PA66	BLACK	MQS HSG., 4POS., COD.B	2
							—		0-1241634-1	B	1	PA66	BLACK	MQS HSG., 4POS., COD.Z	1
Bestell-Nummer Bandware Einzelausführung		DGB in mm²	Werkstoff	Oberfläche	Crimp-Werkzeuge Masch.-Werkz. Handzange		CUSTOMER PART NO	TE CONNECTIVITY PART NO	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION	ITEM NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.

DIMENSIONS:
MASSEHTEITEN
mm

TOLERANCES, UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES / WINKEL ± -

FINISH / OBERFLAECHE / FARBE

MATERIAL

-

DWN
B.Honigmann
03-MAR-99

CHK
H.Schmitt
03 MAR 99

APVD
-

PRODUCT SPEC
PRODUKTSPEZ
-

APPLICATION SPEC
VERARBEITUNGSSPEZ
-

WEIGHT
GEWICHT
-

CUSTOMER DRAWING / KUNDENZEICHNUNG

NAME

MQS SOCKET HOUSING, 4 POS.
MQS Buchsengehaeuse, 4pol.

SIZE
A2

CAGE CODE
00779

DRAWING NO
ZEICHNUNGS-NR.
C=1241634

RESTRICTED TO
NUR FÜR
-

SCALE
MASSTAB 5:1

SHEET
BLATT 1 von 1

REV
B4

1241634