

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [75783-0108](#)
Status: **Active**
Overview: [iPass™ Connector System](#)
Description: iPass™ I/O Surface Mount Receptacle, Right Angle, Internal Assembly with Shell, 36 Circuit, 0.38μm Gold (Au), Retention Option, Tail Length 1.96mm, Right Key

Documents:
[3D Model](#) [Product Specification PS-75783-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family I/O Connectors
Series [75783](#)
Application Wire-to-Board
Comments Positive or passive latching cable available
Component Type Receptacle
Electrical Model Yes
Overview [iPass™ Connector System](#)
Product Name iPass™, PCI Express*, SAS, Serial ATA
Type N/A
UPC 822348852680

Physical

Circuits (Loaded) 36
Circuits (maximum) 36
Color - Resin Black
Durability (mating cycles max) 50
Flammability 94V-0
Gender Female
Keying to Mating Part Yes
Lock to Mating Part None
Material - Metal Copper-Nickel-Zinc, High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 3.069/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 1.96mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.57mm
Packaging Type Embossed Tape on Reel
Panel Mount No
Pitch - Mating Interface 0.80mm
Pitch - Termination Interface 0.80mm
Plating min - Mating 0.381μm
Plating min - Termination 2.540μm
Polarized to Mating Part Yes
Ports 1
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -40°C to +80°C



Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[75783Series](#)

Use With
iPass™ Cable Assemblies, [79575](#) , [79576](#) , [74562](#) , [74563](#) , [79536](#) , [74573](#) , [74569](#) , [74586](#)

Termination Interface: Style	Surface Mount, Through Hole - Kinked Pin
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Voltage - Maximum	30V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability	Reflow Capable (SMT only)
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Electrical Model Document	EE-75586-001
Product Specification	PS-75783-001
Sales Drawing	SD-75783-001

This document was generated on 12/17/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75783-0108