

DS/DSR - DP/DPL - DA SERIES

DIP SWITCHES

Specifications

ELECTRICAL SPECIFICATIONS

- Current/voltage rating :
 - non-switching : 100mA 50VDC
 - switching : 50mA 24VDC
- Contact resistance (at 100mA) :
 - 50mΩ max. at initial
 - 100mΩ after life test
- Insulation resistance (at 100VDC +/-15V) :
 - 100 MΩ min. between adjacent terminals
- Dielectric strength : 500VDC for one minute
- Capacitance : 5 pF between adjacent terminals
- Circuit : single pole, single throw
- Electrical life : 2.000 cycles min. per switch

MATERIALS

- Case, UL94-VO, glass fiber filled PBT, black
- Cover : UL94-VO, glass fiber filled PBT, red
- Actuator : UL94-VO, glass fiber filled PBT, white
- Terminals/contacts : gold over nickel plated phosphor bronze
- Terminal seal : epoxy
- Tape seal : polyester film

GENERAL SPECIFICATIONS

- Operating force :
 - DP models : 4N
 - DS/DA models : 8N
- Travel : 2 mm (.078)
- Mechanical life : 5.000 cycles min. per switch
- Vibration test : MIL-STD-202F method 201A
- Shock test : MIL-STD-202F method 213B, condition A
- Operating temperature : -20°C to +70°C

RECOMMENDED SOLDERING AND CLEANING PROCESSES

- Hand soldering : 320°C max. for 2 seconds max. (30 watt iron max.)
- Wave soldering : 260°C max. for 5 seconds max.
- Force rinse, high agitation or triple bath cleaning method (**with tape seal, option T**) : freon TF or TE. When vapor methods are used, do not subject switch to solvents above 51°C.

Note : keep switches in "OFF" position during soldering and cleaning for best results.

Dimensions : first dimensions are in mm while inches are shown as bracketted numbers.




Packaging unit : standard IC tubes

Quantities depending on model. See table below.

DS/DSR	Quantity	DS-T/DSR-T	Quantity	DA	Quantity	DA-T	Quantity	DP/DPL(-T)	Quantity
DS(R)-02	73	DS(R)-02T	70	DA-02	73	DA-02T	70	DP(L)-02	70
DS(R)-03	52	DS(R)-03T	50	DA-03	52	DA-03T	52	DP(L)-02T	67
DS(R)-04	40	DS(R)-04T	40	DA-04	40	DA-04T	39	DP(L)-03(T)	50
DS(R)-05	33	DS(R)-05T	32	DA-05	33	DA-05T	32	DP(L)-04(T)	39
DS(R)-06	28	DS(R)-06T	28	DA-06	28	DA-06T	28	DP(L)-05(T)	32
DS(R)-07	24	DS(R)-07T	24	DA-07	24	DA-07T	24	DP(L)-06(T)	25
DS(R)-08	21	DS(R)-08T	21	DA-08	21	DA-08T	21	DP(L)-08(T)	21
DS(R)-09	19	DS(R)-09T	19	DA-09	19	DA-09T	19	DP(L)-10(T)	17
DS(R)-10	17	DS(R)-10T	17	DA-10	17	DA-10T	17	DP(L)-12(T)	14
DS(R)-12	14	DS(R)-12T	14	DA-12	14	DA-12T	14		

DS/DSR SERIES

STANDARD DIP SWITCHES




- Raised or recessed actuator
- 2 to 12 positions


MODEL
STRUCTURE



Raised actuator : DS



Model No	No. pos.	Dim "A" (max.)	Dim. "B"
DS-02	2	6,60 (.259)	2,54 (.100)
DS-03	3	9,14 (.359)	5,08 (.200)
DS-04	4	11,68 (.459)	7,62 (.300)
DS-05	5	14,22 (.559)	10,16 (.400)
DS-06	6	16,76 (.659)	12,70 (.500)
DS-07	7	19,30 (.759)	15,24 (.600)
DS-08	8	21,84 (.859)	17,78 (.700)
DS-09	9	24,38 (.959)	20,32 (.800)
DS-10	10	26,92 (1.059)	22,86 (.900)
DS-12	12	32,00 (1.259)	27,94 (1.100)




Top tape sealed : add "T" after model number.

Recessed actuator : DSR




Model No	No. pos.	Dim "A"	Dim. "B"
DSR-02	2	6,60 (.259)	2,54 (.100)
DSR-03	3	9,14 (.359)	5,08 (.200)
DSR-04	4	11,68 (.459)	7,62 (.300)
DSR-05	5	14,22 (.559)	10,16 (.400)
DSR-06	6	16,76 (.659)	12,70 (.500)
DSR-07	7	19,30 (.759)	15,24 (.600)
DSR-08	8	21,84 (.859)	17,78 (.700)
DSR-09	9	24,38 (.959)	20,32 (.800)
DSR-10	10	26,92 (1.059)	22,86 (.900)
DSR-12	12	32,00 (1.259)	27,94 (1.100)



Top tape sealed : add "T" after model number.

DP/DPL SERIES

PIANO DIP SWITCHES




- Short or long actuator
- 2 to 12 positions

Note : Push down for "ON" is our standard type.
Push down for "OFF" is also available on special order,
consult factory.


MODEL
STRUCTURE



Short actuator : DP




Model No	No. pos.	Dim "A" max.	Dim. "B"
DP-02	2	6,63 (.261)	2,54 (.100)
DP-03	3	9,17 (.361)	5,08 (.200)
DP-04	4	11,71 (.461)	7,62 (.300)
DP-05	5	14,25 (.561)	10,16 (.400)
DP-06	6	16,8 (.661)	12,70 (.500)
DP-08	8	21,87 (.861)	17,78 (.700)
DP-10	10	26,95 (1.061)	22,86 (.900)
DP-12	12	32,03 (1.261)	27,94 (1.100)




Top tape sealed : add "T" after model number.

Long actuator : DPL




Model No	No. pos.	Dim "A" max.	Dim. "B"
DPL-02	2	6,63 (.261)	2,54 (.100)
DPL-03	3	9,17 (.361)	5,08 (.200)
DPL-04	4	11,71 (.461)	7,62 (.300)
DPL-05	5	14,25 (.561)	10,16 (.400)
DPL-06	6	16,8 (.661)	12,70 (.500)
DPL-08	8	21,87 (.861)	17,78 (.700)
DPL-10	10	26,95 (1.061)	22,86 (.900)
DPL-12	12	32,03 (1.261)	27,94 (1.100)



Top tape sealed : add "T" after model number.

DA SERIES

RIGHT ANGLE DIP SWITCHES



- 2 to 12 positions

MODEL
STRUCTURE




Raised actuator : DA



Model No	No. pos.	Dim "A"	Dim. "B"
DA-02	2	6,60 (.259)	2,54 (.100)
DA-03	3	9,14 (.359)	5,08 (.200)
DA-04	4	11,68 (.459)	7,62 (.300)
DA-05	5	14,22 (.559)	10,16 (.400)
DA-06	6	16,76 (.659)	12,70 (.500)
DA-07	7	19,30 (.759)	15,24 (.600)
DA-08	8	21,84 (.859)	17,78 (.700)
DA-09	9	24,38 (.959)	20,32 (.800)
DA-10	10	26,92 (1.059)	22,86 (.900)
DA-12	12	32,00 (1.259)	27,94 (1.100)

Top tape sealed : add "T" after model number.



F