


1			2		3		4		5		6		7																																																																																																																						
A	PLUG COMPONENT			PLUG STRIP DIMENSION			SJT 14AWGx3C 60°C Shielded Black Length 1000±20	END STRIP DIMENSION			TERMINAL COMPONENT			A																																																																																																																					
	COLOR	DESCRIPTION	Q'ty	R.I.J	R.O.J	COLOR		R.O.J	R.I.J	COLOR	DESCRIPTION	TYPE																																																																																																																							
	40P BLACK	PVC Compound	1	6 ⁺¹ ₋₀	19 ± 1	BLACK(L)		15 ⁺³ ₋₀		BLACK(L)																																																																																																																									
	Gray color	Assembly Body 111-003-001	1	6 ⁺¹ ₋₀	19 ± 1	WHITE(N)		15 ⁺³ ₋₀		WHITE(N)																																																																																																																									
				6 ⁺¹ ₋₀	19 ± 1	GREEN(E)	15 ⁺³ ₋₀		GREEN(E)																																																																																																																										
B															B																																																																																																																				
C	Plug type Material: - SJT 3 x 14AWG(2.08mm²) VW-1 Shielded, 60°C 300V without Filler - Jacket Color: Black - E - Green; L - Black; N - White Electrical: 100% Open & Short Testing - Insulation Resistance: 100MΩ (min.) - Voltage: 500V DC / 1 minute														C																																																																																																																				
D	Hank Dimension Wire Cross section														D																																																																																																																				
E	BLACK WHITE GREEN COPPER CONDUCTOR (N/mm): 41/0.254±0.005 or Substitute PVC INSULATION AVERAGE THICKNESS: 0.76mm ID: 3.40±0.1mm Aluminum/Mylar(Conducting face drainage wire) Drain wire 7/0.254 or Substitute PVC JACKET AVERAGE THICKNESS: 0.76mm OD: 9.30 ±0.2mm														E																																																																																																																				
F	Unit: mm RoHS Compliant														F																																																																																																																				
G	<table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td colspan="3">Title</td></tr><tr><td colspan="2">TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>10.10.15</td><td>Wilson</td><td colspan="3">Power cord - SJT</td></tr><tr><td>X.</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td>Approved</td><td>10.10.15</td><td>Groll</td><td colspan="3">60°C 14AWG Open End, Shielded 1 Meter</td></tr><tr><td>X.X</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="3">ASSMANN WSW-No.</td></tr><tr><td>X.XX</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="3">AK500/14-OE-5-1</td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="2">Drawing-No.</td><td>rev00</td></tr><tr><td>X.°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="2">Replace</td><td>Sheet</td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="2"></td><td>1/1</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td colspan="3">ASSMANN WSW components 1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us</td><td colspan="4"></td></tr></table>														Scale	Free						Date	Name	Title			TOLERANCE							Drawn	10.10.15	Wilson	Power cord - SJT			X.	±X						Approved	10.10.15	Groll	60°C 14AWG Open End, Shielded 1 Meter			X.X	±X									ASSMANN WSW-No.			X.XX	±X									AK500/14-OE-5-1			DIM	TOL									Drawing-No.		rev00	X.°	±X°									Replace		Sheet	X.X°	±X°											1/1	Angle	TOL	Id.	Modification	Date	Name	ASSMANN WSW components 1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us							G
Scale	Free						Date	Name	Title																																																																																																																										
TOLERANCE							Drawn	10.10.15	Wilson	Power cord - SJT																																																																																																																									
X.	±X						Approved	10.10.15	Groll	60°C 14AWG Open End, Shielded 1 Meter																																																																																																																									
X.X	±X									ASSMANN WSW-No.																																																																																																																									
X.XX	±X									AK500/14-OE-5-1																																																																																																																									
DIM	TOL									Drawing-No.		rev00																																																																																																																							
X.°	±X°									Replace		Sheet																																																																																																																							
X.X°	±X°											1/1																																																																																																																							
Angle	TOL	Id.	Modification	Date	Name	ASSMANN WSW components 1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us																																																																																																																													
H	<table><tr><td colspan="2">1</td><td colspan="2">2</td><td colspan="2">3</td><td colspan="2">4</td><td colspan="2">5</td><td colspan="2">6</td><td colspan="2">7</td></tr></table>														1		2		3		4		5		6		7		H																																																																																																						
1		2		3		4		5		6		7																																																																																																																							