



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		C	REVISED PER ECO-08-027222	05NOV08	HMR	FD

D




RECOMMENDED HOLE LAYOUT
TOLERANCE: ± 0.05 [.002]
UNLESS OTHERWISE NOTED

NOTES:


- 1 MATERIALS:
CONTACT: COPPER ALLOY, 0.004572[.000180] MIN TIN PLATE
OVER 0.00127[.000050] MIN NICKEL.
INSULATOR: PPS, 40% GLASS FILLED, UL 94V-0

- 2 DATE CODE (PER BELOW) TO BE LASER CODED
AND CENTERED ON THIS SURFACE.




3. UL RECOGNITION E320916.

C



B



PART NO.	POS.	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"
1571539-1	20	14.99 [.590]	9.14 [.360]	5.08 [.200]	10.16 [.400]	9.91 [.390]	2.67 [.105]
1571539-2	28	17.53 [.690]	11.68 [.460]	7.62 [.300]	12.70 [.500]	12.45 [.490]	2.67 [.105]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MURREN 25AUG03	Tyco Electronics Corporation Harrisburg, PA 17105-3608				
DIMENSIONS: mm [INCHES]		CHK K. WRIGHT 24APR03					
		APVD K. WRIGHT 24APR03	NAME OUTLINE DRAWING PLCC SOCKET				
		PRODUCT SPEC 108-38000 APPLICATION SPEC					
MATERIAL		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=1571539	RESTRICTED TO -	
FINISH		CUSTOMER DRAWING	SCALE 3:1	SHEET 1 of 1	REV C		