



Rev	AWO #	Description	Date	Appr
-		RELEASED	11/08/04	



654321

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED
PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: PBT, glass reinforced, rated UL 94V-0
 Insulator Color: Black
 Contacts: Phosphor Bronze
 Plating: Tin over Copper underplate overall
 Electrical: Operating voltage: 250 VAC max
 Current rating: 1 Amp max
 Contact resistance: 20 mohms max
 Insulation resistance: 5000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1000 VAC for 1 minute
 Temperature Rating: Operating temperature: -55°C to +105°C
 Packaging: Anti-ESD plastic tubes

A = .100 [2.54] X No. of Positions Per Row
 Positions available: 6, 8, 14, 16, 18, 20, 24 & 26

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES		Holes	
.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010
APPROVALS		DATE	
DRAWN	SS	11/08/04	
CHECKED			
APPROVED			

ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		TITLE IC SOCKET, .300 ROW CENTERS, PCB, TIN PLATED	
SIZE	PART NO.	REV.	
X	ICS-3XX-T	-	
REF:	SCALE: NTS	SHEET 1 OF 1	