


High Intensity SMD LED



19225

DESCRIPTION

The package of the VLMS31.. is the PLCC-2.

It consists of a lead frame which is embedded in a white thermoplast. The reflector inside this package is filled up with clear epoxy.

FEATURES

- SMD LED with exceptional brightness
- Luminous intensity categorized
- Compatible with automatic placement equipment
- EIA and ICE standard package
- Compatible with IR Reflow, vapor phase and wave solder processes according to CECC 00802 and J-STD-020C
- Available in 8 mm tape
- Low profile package
- Non-diffused lens: excellent for coupling to light pipes and backlighting
- Low power consumption
- Luminous intensity ratio in one packaging unit $I_{Vmax}/I_{Vmin} \leq 1.6$
- Lead (Pb)-free device
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC
- Preconditioning acc. to JEDEC Level 2a
- ESD-withstand voltage: up to 2 kV according to JESD22-A114-B



APPLICATIONS

- Automotive: Backlighting in dashboards and switches
- Telecommunication: Indicator and backlighting in telephone and fax
- Indicator and backlight for audio and video equipment
- Indicator and backlight in office equipment
- Flat backlight for LCDs, switches and symbols
- General use

PARTS TABLE

PART	COLOR, LUMINOUS INTENSITY	ANGLE OF HALF INTENSITY ($\pm \phi$)	TECHNOLOGY
VLMS31J1K2-GS08	Red, $I_V = (4.5 \text{ to } 11.2) \text{ mcd}$	60°	GaAsP on GaP
VLMS31J1K2-GS18	Red, $I_V = (4.5 \text{ to } 11.2) \text{ mcd}$	60°	GaAsP on GaP
VLMS31J1L2-GS08	Red, $I_V = (4.5 \text{ to } 18) \text{ mcd}$	60°	GaAsP on GaP
VLMS31J1L2-GS18	Red, $I_V = (4.5 \text{ to } 18) \text{ mcd}$	60°	GaAsP on GaP
VLMS31K1L2-GS08	Red, $I_V = (7.1 \text{ to } 18) \text{ mcd}$	60°	GaAsP on GaP
VLMS31K1L2-GS18	Red, $I_V = (7.1 \text{ to } 18) \text{ mcd}$	60°	GaAsP on GaP

ABSOLUTE MAXIMUM RATINGS ¹⁾ , VLMS31..				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage ²⁾		V_R	6	V
DC Forward current	$T_{amb} \leq 85\text{ }^{\circ}\text{C}$	I_F	30	mA
Surge forward current	$t_p \leq 10\text{ }\mu\text{s}$	I_{FSM}	0.1	A
Power dissipation		P_V	80	mW
Junction temperature		T_j	100	$^{\circ}\text{C}$
Operating temperature range		T_{amb}	- 40 to + 100	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	- 40 to + 100	$^{\circ}\text{C}$
Thermal resistance junction/ ambient	mounted on PC board (pad size > 16 mm ²)	R_{thJA}	400	K/W

Note:

¹⁾ $T_{amb} = 25\text{ }^{\circ}\text{C}$ unless otherwise specified

²⁾ Driving LED in reverse direction is suitable for short term application

OPTICAL AND ELECTRICAL CHARACTERISTICS ¹⁾ , VLMS31.., RED							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN	TYP.	MAX	UNIT
Luminous intensity ²⁾	$I_F = 10\text{ mA}$	VLMS31J1K2	I_V	4.5		11.2	mcd
		VLMS31J1L2	I_V	4.5		18	mcd
		VLMS31K1L2	I_V	7.1		18	mcd
Dominant wavelength	$I_F = 10\text{ mA}$		λ_d	624	630	638	nm
Peak wavelength	$I_F = 10\text{ mA}$		λ_p		643		nm
Angle of half intensity	$I_F = 10\text{ mA}$		φ		± 60		deg
Forward voltage	$I_F = 20\text{ mA}$		V_F		1.9	2.6	V
Reverse voltage	$I_R = 10\text{ }\mu\text{A}$		V_R	5			V
Junction capacitance	$V_R = 0, f = 1\text{ MHz}$		C_j		15		pF

Note:

¹⁾ $T_{amb} = 25\text{ }^{\circ}\text{C}$ unless otherwise specified

²⁾ in one Packing Unit $I_{Vmax}/I_{Vmin} \leq 2.0$

LUMINOUS INTENSITY CLASSIFICATION			
GROUP	LIGHT INTENSITY [MCD]		
STANDARD	OPTIONAL	MIN	MAX
J	1	4.5	5.6
	2	5.6	7.1
K	1	7.1	9.0
	2	9.0	11.2
L	1	11.2	14
	2	14	18

Note:

Luminous intensity is tested at a current pulse duration of 25 ms and an accuracy of $\pm 11\%$.

The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each reel (there will be no mixing of two groups on each reel).

In order to ensure availability, single brightness groups will not be orderable.

In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped on any one reel.

In order to ensure availability, single wavelength groups will not be orderable.

CROSSING TABLE	
VISHAY	OSRAM
VLMS31J1K2	LST670-J1K2
VLMS31J1L2	LST670-J1L2
VLMS31K1L2	LST670-K1L2

TYPICAL CHARACTERISTICS

$T_{amb} = 25\text{ }^{\circ}\text{C}$ unless otherwise specified




Figure 1. Forward Current vs. Ambient Temperature




Figure 4. Relative Luminous Intensity vs. Wavelength




Figure 2. Forward Current vs. Pulse Length




Figure 5. Forward Current vs. Forward Voltage




Figure 3. Rel. Luminous Intensity vs. Angular Displacement




Figure 6. Relative Luminous Intensity vs. Forward Current




Figure 7. Rel. Luminous Intensity vs. Ambient Temperature




Figure 9. Change of Forward Voltage vs. Ambient Temperature






Figure 8. Change of Dominant Wavelength vs. Ambient Temperature


PACKAGE DIMENSIONS IN MM



Drawing-No. : 6.541-5025.01-4
Issue: 8; 22.11.05

95 11314-1


Mounting Pad Layout



METHOD OF TAPING/POLARITY AND TAPE AND REEL

SMD LED (VLM3 - SERIES)

Vishay's LEDs in SMD packages are available in an antistatic 8 mm blister tape (in accordance with DIN IEC 40 (CO) 564) for automatic component insertion. The blister tape is a plastic strip with impressed component cavities, covered by a top tape.



TAPING OF VLM.3..




Figure 10. Tape dimensions in mm for PLCC-2

REEL PACKAGE DIMENSION IN MM FOR SMD LEDs, TAPE OPTION GS08 (= 1500 PCS.)




Figure 11. Reel dimensions - GS08

REEL PACKAGE DIMENSION IN MM FOR SMD LEDs, TAPE OPTION GS18 (= 8000 PCS.) PREFERRED




Figure 12. Reel dimensions - GS18

SOLDERING PROFILE




Figure 13. Vishay Lead (Pb)-free Reflow Soldering Profile (acc. to J-STD-020C)





Figure 14. Double wave soldering of opto devices (all packages)


BARCODE-PRODUCT-LABEL



- A) Type of component
- B) Manufacturing plant
- C) SEL - Selection Code (Bin):
e.g.: J1 = Code for Luminous Intensity Group
- D) Date Code year/week
- E) Day Code (e.g. 3: Wednesday)
- F) Batch No.
- G) Total quantity
- H) Company Code

DRY PACKING

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



FINAL PACKING

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.

RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the aluminium bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity $\leq 60\%$ RH max.

After more than 672 hours under these conditions moisture content will be too high for reflow soldering.

In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

192 hours at 40 °C + 5 °C/ - 0 °C and < 5 % RH (dry air/nitrogen) or

96 hours at 60 °C + 5 °C and < 5 % RH for all device containers or

24 hours at 100 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC Standard JESD22-A112 Level 2a label is included on all dry bags.

	CAUTION This bag contains MOISTURE - SENSITIVE DEVICES	LEVEL 2a						
1. Shelf life in sealed bag 12 months at <40°C and < 90% relative humidity (RH)								
2. After this bag is opened devices that will be subjected to infrared reflow, vapor-phase reflow, or equivalent processing (peak package body temp. 260°C) must be: a) Mounted within 672 hours at factory condition of $\leq 30^\circ\text{C}/60\%\text{RH}$ or b) Stored at $\leq 10\%\text{RH}$.								
3. Devices require baking before mounting if: a) Humidity Indicator Card is >10% when read at $23^\circ\text{C} \pm 5^\circ\text{C}$ or b) 2a or 2b is not met.								
4. If baking is required, devices may be baked for: <table border="0" style="width: 100%;"> <tr> <td>192 hours at $40^\circ\text{C} + 5^\circ\text{C}/-0^\circ\text{C}$ and <5%RH (dry air/nitrogen)</td> <td style="text-align: right;">or</td> </tr> <tr> <td>96 hours at $60 \pm 5^\circ\text{C}$ and <5%RH</td> <td style="text-align: right;">For all device containers or</td> </tr> <tr> <td>24 hours at $100 \pm 5^\circ\text{C}$</td> <td style="text-align: right;">Not suitable for reels or tubes</td> </tr> </table>			192 hours at $40^\circ\text{C} + 5^\circ\text{C}/-0^\circ\text{C}$ and <5%RH (dry air/nitrogen)	or	96 hours at $60 \pm 5^\circ\text{C}$ and <5%RH	For all device containers or	24 hours at $100 \pm 5^\circ\text{C}$	Not suitable for reels or tubes
192 hours at $40^\circ\text{C} + 5^\circ\text{C}/-0^\circ\text{C}$ and <5%RH (dry air/nitrogen)	or							
96 hours at $60 \pm 5^\circ\text{C}$ and <5%RH	For all device containers or							
24 hours at $100 \pm 5^\circ\text{C}$	Not suitable for reels or tubes							
Bag Seal Date: _____ (If blank, see bar code label)								
Note: LEVEL defined by EIA JEDEC Standard JESD22-A113								

19786

Example of JESD22-A112 Level 2a label

ESD PRECAUTION

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the Antistatic Shielding Bag. Electro-Static Sensitive Devices warning labels are on the packaging.

VISHAY SEMICONDUCTORS STANDARD BAR-CODE LABELS

The Vishay Semiconductors standard bar-code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.

**OZONE DEPLETING SUBSTANCES POLICY STATEMENT**

It is the policy of Vishay Semiconductor GmbH to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design
and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.