

8132 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485

For more Information
please call

1-800-Belden1

**General Description:**

28 AWG stranded (7x36) TC conductors, Datalene® insulation, overall Beldfoil® (100% coverage) + TC braid shield (65% coverage), 28 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
2	28	7x36	TC - Tinned Copper

Total Number of Conductors: 4

Insulation**Insulation Material:**

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Datalene®	FPE - Foam Polyethylene	0.381

Outer Shield**Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100
2		Braid	TC - Tinned Copper	65

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
28	7x36	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.889

Overall Cable

Overall Nominal Diameter: 5.588 mm

Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2919)
Bulk Cable Weight:	38.693 Kg/Km
Min. Bend Radius/Minor Axis:	57.150 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CL2

8132 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485

AWM Specification:	UL Style 2919 (30 V 80°C)
--------------------	---------------------------

EU Directive 2011/65/EU (ROHS II):	Yes
------------------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

120

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

36.091

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

65.62

Nominal Velocity of Propagation:

VP (%)

78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

213.265

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

16.7331

Max. Operating Voltage - UL:

Voltage	Description
30 V RMS	UL AWM Style 2919
150 V RMS	CL2

Max. Recommended Current:

Current

1 Amp per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8132 060100	30 MT	1.497 KG	CHROME		2 PR #28 FHDPE SH PVC
8132 0601000	305 MT	13.154 KG	CHROME	C	2 PR #28 FHDPE SH PVC

METRIC MEASUREMENT VERSION

8132 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485

8132 060500	152 MT	6.577 KG	CHROME	C	2 PR #28 FHDPE SH PVC
8132 0605000	1,524 MT	68.039 KG	CHROME		2 PR #28 FHDPE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 10-01-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.