

			<table><tr><th colspan="4">REVISIONS</th></tr><tr><th>REV</th><th>DESCRIPTION</th><th>DATE</th><th>APPROVED</th></tr><tr><td>022</td><td>ECN 92-0010</td><td>1/12/93</td><td>1/14/93</td></tr></table>				REVISIONS				REV	DESCRIPTION	DATE	APPROVED	022	ECN 92-0010	1/12/93	1/14/93																																																																							
			REVISIONS																																																																																						
			REV	DESCRIPTION	DATE	APPROVED																																																																																			
022	ECN 92-0010	1/12/93	1/14/93																																																																																						
<table><tr><td>HOUSING COUPLING NUT</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td colspan="2">GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290</td></tr><tr><td>DIELECTRIC</td><td>TFE FLUOROCARBON PER ASTM-D-1457</td><td colspan="2">N/A</td></tr><tr><td>CENTER CONTACT</td><td>BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H</td><td colspan="2">GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550</td></tr><tr><td>RETAINING RING</td><td>BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H</td><td colspan="2">N/A</td></tr><tr><td>GASKET</td><td>SILICONE RUBBER PER ZZ-R-765</td><td colspan="2">N/A</td></tr></table>				HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290		DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A		CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550		RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A		GASKET	SILICONE RUBBER PER ZZ-R-765	N/A																																																																			
HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290																																																																																							
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A																																																																																							
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550																																																																																							
RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A																																																																																							
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A																																																																																							
<table><tr><th>ELECTRICAL</th><th>MECHANICAL</th><th>ENVIRONMENTAL</th></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions MIL-STD-348A, OSM Fig. 310.2</td><td>Temperature Rating -65°C to +125°C</td></tr><tr><td>Frequency Range (GHz) DC to 25</td><td>OSSM Fig. 319.1</td><td>Vibration MIL-STD-202, Method 204, Condition D.</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 250</td><td>Recommended Mating Torque PLUG END 5 ±.5 in-lbs</td><td>Shock MIL-STD-202, Method 213, Condition I.</td></tr><tr><td>VSWR DC - 12.4 (GHz)-1.06 +.009 f(GHz) 12.4 - 25.0 (GHz)-1.05 +.01 f(GHz)</td><td>Mating Characteristics OSM END: Insertion (MAX Lbs) 3.0</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B, except high temp shall be +85°C</td></tr><tr><td>Insertion Loss (dB MAX) .06 √f(GHz)</td><td>Withdrawal (MIN Oz) 1.0</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>RF Leakage (dB MIN) [-(60-f(GHz))]</td><td>Force to Engage and Disengage (In-Lbs MAX) 2.0</td><td>Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 190</td><td>Center Contact Captivation Axial (Lbs) 6.0</td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750</td><td>Radial (In-Oz) 4.0</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX) Center Contact 2.0</td><td>Cable Retention Axial Force (Lbs) N/A</td><td></td></tr><tr><td>Outer Contact 2.0</td><td>Torque (In-Oz) N/A</td><td></td></tr><tr><td>Cable to Housing N/A</td><td>Weight (Grams) 2.9</td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500</td><td></td><td></td></tr><tr><td>I.R.(Megohms MIN) 5,000</td><td></td><td></td></tr></table>		ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, OSM Fig. 310.2	Temperature Rating -65°C to +125°C	Frequency Range (GHz) DC to 25	OSSM Fig. 319.1	Vibration MIL-STD-202, Method 204, Condition D.	Volt Rating (VRMS MAX) @ Sea Level 250	Recommended Mating Torque PLUG END 5 ±.5 in-lbs	Shock MIL-STD-202, Method 213, Condition I.	VSWR DC - 12.4 (GHz)-1.06 +.009 f(GHz) 12.4 - 25.0 (GHz)-1.05 +.01 f(GHz)	Mating Characteristics OSM END: Insertion (MAX Lbs) 3.0	Thermal Shock MIL-STD-202, Method 107, Condition B, except high temp shall be +85°C	Insertion Loss (dB MAX) .06 √f(GHz)	Withdrawal (MIN Oz) 1.0	Moisture Resistance MIL-STD-202, Method 106	RF Leakage (dB MIN) [-(60-f(GHz))]	Force to Engage and Disengage (In-Lbs MAX) 2.0	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray	Corona, 70,000 Ft (VRMS MIN) 190	Center Contact Captivation Axial (Lbs) 6.0		Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750	Radial (In-Oz) 4.0		Contact Resistance (Milliohms MAX) Center Contact 2.0	Cable Retention Axial Force (Lbs) N/A		Outer Contact 2.0	Torque (In-Oz) N/A		Cable to Housing N/A	Weight (Grams) 2.9		RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500			I.R.(Megohms MIN) 5,000			<table><tr><td colspan="2">UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON</td><td colspan="2">DRAWN BY E.J.C. DATE 7/12/68</td><td rowspan="3"></td><td rowspan="3">AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td colspan="2">FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°</td><td colspan="2">CHECKED BY PRB DATE 7/16/68</td></tr><tr><td colspan="2"></td><td colspan="2">APPD BY DATE 7/17/68</td></tr><tr><td colspan="2">These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td colspan="2">USE ASS'Y PROCEDURE</td><td colspan="2">TITLE OSM JACK TO OSSM PLUG ADAPTER</td></tr><tr><td colspan="2"></td><td colspan="2">NO. AP. N/A</td><td>SIZE B</td><td>CODE IDENT NO. 26805</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">2082-2201-00</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td>SCALE 8 : 1</td><td>REV 022</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">SHEET 1 OF 1</td></tr></table>		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON		DRAWN BY E.J.C. DATE 7/12/68			AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		CHECKED BY PRB DATE 7/16/68				APPD BY DATE 7/17/68		These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		USE ASS'Y PROCEDURE		TITLE OSM JACK TO OSSM PLUG ADAPTER				NO. AP. N/A		SIZE B	CODE IDENT NO. 26805					2082-2201-00						SCALE 8 : 1	REV 022					SHEET 1 OF 1	
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																																							
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, OSM Fig. 310.2	Temperature Rating -65°C to +125°C																																																																																							
Frequency Range (GHz) DC to 25	OSSM Fig. 319.1	Vibration MIL-STD-202, Method 204, Condition D.																																																																																							
Volt Rating (VRMS MAX) @ Sea Level 250	Recommended Mating Torque PLUG END 5 ±.5 in-lbs	Shock MIL-STD-202, Method 213, Condition I.																																																																																							
VSWR DC - 12.4 (GHz)-1.06 +.009 f(GHz) 12.4 - 25.0 (GHz)-1.05 +.01 f(GHz)	Mating Characteristics OSM END: Insertion (MAX Lbs) 3.0	Thermal Shock MIL-STD-202, Method 107, Condition B, except high temp shall be +85°C																																																																																							
Insertion Loss (dB MAX) .06 √f(GHz)	Withdrawal (MIN Oz) 1.0	Moisture Resistance MIL-STD-202, Method 106																																																																																							
RF Leakage (dB MIN) [-(60-f(GHz))]	Force to Engage and Disengage (In-Lbs MAX) 2.0	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray																																																																																							
Corona, 70,000 Ft (VRMS MIN) 190	Center Contact Captivation Axial (Lbs) 6.0																																																																																								
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750	Radial (In-Oz) 4.0																																																																																								
Contact Resistance (Milliohms MAX) Center Contact 2.0	Cable Retention Axial Force (Lbs) N/A																																																																																								
Outer Contact 2.0	Torque (In-Oz) N/A																																																																																								
Cable to Housing N/A	Weight (Grams) 2.9																																																																																								
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500																																																																																									
I.R.(Megohms MIN) 5,000																																																																																									
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON		DRAWN BY E.J.C. DATE 7/12/68			AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																																																				
FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		CHECKED BY PRB DATE 7/16/68																																																																																							
		APPD BY DATE 7/17/68																																																																																							
These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		USE ASS'Y PROCEDURE		TITLE OSM JACK TO OSSM PLUG ADAPTER																																																																																					
		NO. AP. N/A		SIZE B	CODE IDENT NO. 26805																																																																																				
				2082-2201-00																																																																																					
				SCALE 8 : 1	REV 022																																																																																				
				SHEET 1 OF 1																																																																																					