



# Intel® Pentium® Processor E5200

2M Cache, 2.50 GHz, 800 MHz FSB

[Add to Compare](#)[Specifications](#)

## Essentials

[Performance](#)[Supplemental Information](#)[Package Specifications](#)[Advanced Technologies](#)[Security & Reliability](#)[Ordering and Compliance](#)[Product Images](#)[Compatible Products](#)[Downloads and Software](#)

## Essentials

[Export specifications](#)[Product Collection](#)[Legacy Intel® Pentium® Processor](#)[Code Name](#)[Products formerly Wolfdale](#)[Vertical Segment](#)[Desktop](#)[Processor Number](#)[E5200](#)[Status](#)[Discontinued](#)[Launch Date](#) [Q3'08](#)[Lithography](#) [45 nm](#)[Recommended Customer Price](#) 

## Performance

[# of Cores](#) [2](#)[Processor Base Frequency](#) [2.50 GHz](#)[Cache](#) [2 MB L2](#)[Bus Speed](#) [800 MHz FSB](#)[FSB Parity](#) [No](#)[TDP](#) [65 W](#)[VID Voltage Range](#) [0.8500V-1.3625V](#)

## Supplemental Information

[Embedded Options Available](#) [No](#)[Datasheet](#)[View now](#)

## Package Specifications

[Sockets Supported](#) [LGA775](#)[Max CPU Configuration](#)[1](#)[T<sub>CASE</sub>](#) [74.1°C](#)[Package Size](#)[37.5mm x 37.5mm](#)[Processing Die Size](#)[82 mm<sup>2</sup>](#)[# of Processing Die Transistors](#)[228 million](#)

## Advanced Technologies

[Intel® Turbo Boost Technology<sup>†</sup>](#) [No](#)

Intel® Hyper-Threading Technology <sup>‡</sup> 	No
Intel® Virtualization Technology (VT-x) 	No
Intel® Virtualization Technology for Directed I/O (VT-d) <sup>‡</sup> 	No
Intel® 64 <sup>‡</sup> 	Yes
Instruction Set 	64-bit
Idle States 	Yes
Enhanced Intel SpeedStep® Technology 	Yes
Intel® Demand Based Switching 	No
Thermal Monitoring Technologies 	Yes

## Security & Reliability

Intel® AES New Instructions 	No
Intel® Trusted Execution Technology <sup>‡</sup> 	No
Execute Disable Bit <sup>‡</sup> 	Yes

More support options for Intel® Pentium® Processor E5200 (2M Cache, 2.50 GHz, 800 MHz FSB)



[Product Support](#)



[Downloads and Software](#)



[Support Community](#)



[Warranty and Replacement](#)



Need more help?

[Contact support](#)



[Give Feedback](#)

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is" and Intel does not make any representations or warranties whatsoever regarding accuracy of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

Intel classifications are for informational purposes only and consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company as an importer and/or exporter is responsible for determining the correct classification of your transaction.

Refer to Datasheet for formal definitions of product properties and features.

"Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

Some products can support AES New Instructions with a Processor Configuration update, in particular, i7-2630QM/i7-2635QM, i7-2670QM/i7-2675QM, i5-2430M/i5-2435M, i5-2410M/i5-2415M. Please contact OEM for the BIOS that includes the latest Processor configuration update.

<sup>‡</sup> This feature may not be available on all computing systems. Please check with the system vendor to determine if your system delivers this feature, or reference the system specifications (motherboard, processor, chipset, power supply, HDD, graphics controller, memory, BIOS, drivers, virtual machine monitor-VMM, platform software, and/or operating system) for feature compatibility. Functionality, performance, and other benefits of this feature may vary depending on system configuration.

See <http://www.intel.com/content/www/us/en/architecture-and-technology/hyper-threading/hyper-threading-technology.html?wapkw=hyper+threading> for more information including details on which processors support Intel® HT Technology.

Max Turbo Frequency refers to the maximum single-core processor frequency that can be achieved with Intel® Turbo Boost Technology. See [www.intel.com/technology/turboboot/](http://www.intel.com/technology/turboboot/) for more information.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers, typically represent 1,000-unit purchase quantities, and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and

shipment quantities, and special promotional arrangements may apply. If sold in bulk, price represents individual unit. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

System and Maximum TDP is based on worst case scenarios. Actual TDP may be lower if not all I/Os for chipsets are used.

For benchmarking data see <http://www.intel.com/performance>.

Intel processor numbers are not a measure of performance. Processor numbers differentiate features within each processor family, not across different processor families. See <http://www.intel.com/content/www/us/en/processors/processor-numbers.html> for details.

Processors that support 64-bit computing on Intel® architecture require an Intel 64 architecture-enabled BIOS.

Company Information   Our Commitment   Communities   Investor Relations   Contact Us

Newsroom   Jobs



© Intel Corporation   |   [Terms of Use](#)   |   [\\*Trademarks](#)   |   [Privacy](#)   |   [Cookies](#)   |   [Supply Chain Transparency](#)   |   [Site Map](#)