


| Date | SYM | REVISION RECORD | AUTH | DR. | CK. |
|----------|-----|-----------------------------|------|------|-----|
| 3/05/10 | J | Updated PCB Layout | T.B. | B.S. | |
| 4/25/14 | K | Updated to ROHS 2 Compliant | T.B. | B.S. | |
| 01/27/17 | L | Updated UL File number | T.B. | B.S. | |
| | | | | | |
| | | | | | |
| | | | | | |



SPECIFICATIONS:

- * Holder material- Zenite 30% glass reinforced Liquid Crystal Polymer resin, UL File No. E344082, UL94V-0
- * Color: Off White
- * Contacts : 0.020" thick PHOS-BRONZE, GOLD FLASH
- * Temperature range: -40°C to +280°C
- * Vibration Test: 10-50-10 Hz swept in 60 seconds X,Y,Z direction: 1 hour each direction
- * Result: No dislodgement of the cell or damage No discontinuity over 10 micro-seconds
- * Shock Test: Half sine wave acceleration 150G. 6 ms 3 shock pulses each direction per axis, total of 18 pulses
- * Result: No evidence of physical damage
- * ROHS 2 COMPLIANT

| | | | | |
|--------------------------------|---|---------------------------------|-------|------------------|
| Tolerance (Except as noted) |  MPD | Memory Protection Devices, Inc | | |
| decimal ± .5 (.020) | | | Scale | Drawn By B.S. |
| | | | | Approved By T.B. |
| Fractional ± .8 (.030) | Title SURFACE MOUNT BATTERY HOLDER FOR CR2032 | | | |
| Angular ± 3° | Date 01/27/17 | Drawing Number BU2032SM-HD-G | | |