





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		D	ECR-15-001456	31JAN2015	M.P.	M.G.
			D1	ECR-15-011013	29JUL2015	M.P.	M.G.
			D2	REVISED PER ECO-17-001706	10FEB2017	C.A.	M.G.


SECTION C-C






—Ø18: DIAMETRO MINIMO DI UN FORO ATTRAVERSO IL
QUALE IL CONNETTORE PUO' PASSARE
(MINIMUM HOLE DIAMETER THE
CONNECTOR CAN PASS THROUGH)



P/N 284703-1 AS SHOWN
(CODING A)




VISTA CON SECONDARY LOCK CHIUSO
(VIEW WITH SECONDARY LOCK IN CLOSED POSITION)


REVISIONE PRODOTTO
(PRODUCT REVISION)

- 1) LE CAVITA' SONO ADATTE PER INSERIRE I CONTATTI MQS:
P/N 962885-... (0.35-0.5 mmq) E 965906-... (0.75 mmq) CON I RELATIVI
GOMMINI PASSACAVO P/Ns 967067-1/-2.
VEDERE LA SPECIFICA DI APPLICAZIONE 114-18025 PER LA CORRETTA AGGRAFFATURA
(CAVITIES ARE SUITABLE FOR MQS SOCKET CONTACTS :
P/N 962885-... (0.35-0.5sqmm) AND 965906-... (0.75sqmm) AND RELEVANT
SINGLE WIRE SEAL P/Ns 967067-1/-2
SEE APPLICATION SPEC. No. 114-18025 FOR CORRECT WIRE CRIMP PARAMETERS)
- 2) STATO DI FORNITURA, SECONDARY LOCK IN POSIZIONE PREASSEMBLATA
(SUPPLYING CONDITION, SECONDARY LOCK IN PRE-ASSEMBLED POSITION)
- 3) SECONDARY LOCK IN POSIZIONE CHIUSA (DOPO L'INSERIMENTO DEI CONTATTI IN
CAVITA') PER LA CONNESSIONE CON LA CONTROPARTE
(SECONDARY LOCK IN CLOSED POSITION (AFTER CONTACTS INSERTION INTO CAVITIES)
FOR MATING ONTO COUNTERPART)
- 4) ACCOPPIABILE CON DIMA IN ACCORDO ALLA SPEC. 114-18063-122 E CON CONNETTORE
P/N 1-967079-3
(MATEABLE WITH INTERFACE ACCORDING TO SPEC. 114-18063-122 AND WITH PIN
CONNECTOR P/N 1-967079-3


CODICI DI POLARIZZAZIONE / (POLARIZATION CODINGS)



P/N 284703-1
CODICE A / (CODING A)
SECONDARY LOCK COLORE VERDE
(SECONDARY LOCK GREEN COLOUR)



P/N 284703-2
CODICE B / (CODING B)
SECONDARY LOCK COLORE GRIGIO
(SECONDARY LOCK GREY COLOUR)



P/N 284703-3
CODICE C / (CODING C)
SECONDARY LOCK COLORE BLU
(SECONDARY LOCK BLUE COLOUR)

I	NERO/(BLACK)	PA66 GF	BLOCCHETTO/(HOUSING)	3	
I	TRASPARENTE/(TRANSPARENT)	LSR	GUARNIZIONE/(SEALING)	2	
I	VED. TABELLA CODICI POLARIZ. (SEE POLARIZATION CODINGS TABLE)	PA66 GF	SECONDARY LOCK	1	
Q.TA' (Q.TY)	COLORE (COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)	NO. (ITEM)	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. PLAZIO 30MAR2011	 TE Connectivity		
		CHK R. MARTINI 30MAR2011			
DIMENSIONS:		APVD A. GENTA 30MAR2011	NAME 2 POS. MQS SOCKET ASS'Y		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-20234			
mm	0 PLC ±0.3 1 PLC ±0.3 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±±	APPLICATION SPEC 411-20066	SIZE CAGE CODE DRAWING NO A260779 C-284703		
MATERIAL	FINISH	WEIGHT -			RESTRICTED TO -
SEE TABLE	-	Customer Drawing	SCALE 3:1	SHEET 1 OF 1	