


# 3M™ Pak 5 Socket

0.5 mm Straight Stacking, Surface Mount

PK5 Series



- 0.5 mm pitch high density connector conserves board space
- Mated heights available from 4 to 8 mm
- Surface mount design allows for easy inspection and repair of solder joints
- Tape and reel packaging available
- RoHS\* compliant

Date Modified: July 10, 2006

TS-1149-02  
Sheet 1 of 5

## Physical

### Insulation

Material: Glass filled LCP  
Flammability: UL 94V-0  
Color: White

### Contact

Material: Copper Alloy

### Plating

Underplating: Nickel  
Wiping Area: 2  $\mu$ " [ 0.05  $\mu$ m ] min. Gold over Nickel  
Solder Tails: Gold over Nickel

## Electrical

**Current Rating:** 0.3 A

**Insulation Resistance:** 10<sup>3</sup> M $\Omega$  min at 250 VDC

**Withstanding Voltage:** 200 VAC for 1 minute

## Environmental

**Temperature Rating:** -55°C to +85°C

**Process Rating:** 260°C (per J-STD-020C)

\* RoHS = Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment  
"RoHS compliant" means that the product or part does not contain any of the following substances in excess of the following maximum concentration values in any homogeneous material, unless the substance is in an application that is exempt under RoHS: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers; or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's knowledge and belief based upon information provided by third party suppliers to 3M.

# 3M™ Pak 5 Socket

0.5 mm Straight Stacking, Surface Mount




PK5 Series

Socket for 4 and 6 mm stacked height.


Product Table / Dimensions

| Contact Quantity | A       | B       | C       | D       | E       | F       | G       | H       |
|------------------|---------|---------|---------|---------|---------|---------|---------|---------|
| 40               | 9.50    | 10.82   | 11.62   | 13.22   | 10.50   | 11.76   | 14.54   | 13.59   |
|                  | [0.374] | [0.426] | [0.457] | [0.520] | [0.413] | [0.463] | [0.572] | [0.535] |
| 50               | 12.00   | 13.32   | 14.12   | 15.72   | 13.00   | 14.26   | 17.04   | 16.09   |
|                  | [0.472] | [0.524] | [0.556] | [0.619] | [0.512] | [0.561] | [0.671] | [0.633] |
| 60               | 14.50   | 15.82   | 16.62   | 18.22   | 15.50   | 16.76   | 19.54   | 18.59   |
|                  | [0.571] | [0.623] | [0.654] | [0.717] | [0.610] | [0.660] | [0.769] | [0.732] |
| 80               | 19.50   | 20.82   | 21.62   | 23.22   | 20.50   | 21.76   | 24.54   | 23.59   |
|                  | [0.768] | [0.820] | [0.851] | [0.914] | [0.807] | [0.857] | [0.966] | [0.929] |
| 100              | 24.50   | 25.82   | 26.62   | 28.22   | 25.50   | 26.76   | 29.54   | 28.59   |
|                  | [0.965] | [1.017] | [1.048] | [1.111] | [1.004] | [1.054] | [1.163] | [1.126] |
| 120              | 29.50   | 30.82   | 31.62   | 33.22   | 30.50   | 31.76   | 34.54   | 33.59   |
|                  | [1.161] | [1.213] | [1.245] | [1.308] | [1.201] | [1.250] | [1.360] | [1.322] |
| 140              | 34.50   | 35.82   | 36.62   | 38.22   | 35.50   | 36.76   | 39.54   | 38.59   |
|                  | [1.358] | [1.410] | [1.442] | [1.505] | [1.398] | [1.447] | [1.557] | [1.519] |
| 160              | 39.50   | 40.82   | 41.62   | 43.22   | 40.50   | 41.76   | 44.54   | 43.59   |
|                  | [1.555] | [1.607] | [1.639] | [1.702] | [1.594] | [1.644] | [1.754] | [1.716] |

Printed Circuit Board Layout  
(Component Side View)



X-X' Cross Section



TS-1149-02  
Sheet 2 of 5



Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call

800-225-5373

# 3M™ Pak 5 Socket

0.5 mm Straight Stacking, Surface Mount



PK5 Series

Socket for 5 and 7 mm stacked height.


Product Table / Dimensions

| Contact Quantity | A                | B                | C                | D                | E                | F                | G                | H                |
|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|
| 40               | 9.50<br>[0.374]  | 10.82<br>[0.426] | 11.62<br>[0.457] | 13.22<br>[0.520] | 10.50<br>[0.413] | 11.76<br>[0.463] | 14.54<br>[0.572] | 13.59<br>[0.535] |
| 50               | 12.00<br>[0.472] | 13.32<br>[0.524] | 14.12<br>[0.556] | 15.72<br>[0.619] | 13.00<br>[0.512] | 14.26<br>[0.561] | 17.04<br>[0.671] | 16.09<br>[0.633] |
| 60               | 14.50<br>[0.571] | 15.82<br>[0.623] | 16.62<br>[0.654] | 18.22<br>[0.717] | 15.50<br>[0.610] | 16.76<br>[0.660] | 19.54<br>[0.769] | 18.59<br>[0.732] |
| 80               | 19.50<br>[0.768] | 20.82<br>[0.820] | 21.62<br>[0.851] | 23.22<br>[0.914] | 20.50<br>[0.807] | 21.76<br>[0.857] | 24.54<br>[0.966] | 23.59<br>[0.929] |
| 100              | 24.50<br>[0.965] | 25.82<br>[1.017] | 26.62<br>[1.048] | 28.22<br>[1.111] | 25.50<br>[1.004] | 26.76<br>[1.054] | 29.54<br>[1.163] | 28.59<br>[1.126] |
| 120              | 29.50<br>[1.161] | 30.82<br>[1.213] | 31.62<br>[1.245] | 33.22<br>[1.308] | 30.50<br>[1.201] | 31.76<br>[1.250] | 34.54<br>[1.360] | 33.59<br>[1.322] |
| 140              | 34.50<br>[1.358] | 35.82<br>[1.410] | 36.62<br>[1.442] | 38.22<br>[1.505] | 35.50<br>[1.398] | 36.76<br>[1.447] | 39.54<br>[1.557] | 38.59<br>[1.519] |
| 160              | 39.50<br>[1.555] | 40.82<br>[1.607] | 41.62<br>[1.639] | 43.22<br>[1.702] | 40.50<br>[1.594] | 41.76<br>[1.644] | 44.54<br>[1.754] | 43.59<br>[1.716] |

X-X' Cross Section



Printed Circuit Board Layout  
(Component Side View)



TS-1149-02  
Sheet 3 of 5

3M

Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call

800-225-5373

# 3M™ Pak 5 Socket

0.5 mm Straight Stacking, Surface Mount



PK5 Series

Socket for 6 and 8 mm stacked height.


Product Table / Dimensions

| Contact Quantity | A                | B                | C                | D                | E                | F                | G                | H                |
|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|
| 40               | 9.50<br>[0.374]  | 10.82<br>[0.426] | 11.62<br>[0.457] | 13.22<br>[0.520] | 10.50<br>[0.413] | 11.76<br>[0.463] | 14.54<br>[0.572] | 13.59<br>[0.535] |
| 50               | 12.00<br>[0.472] | 13.32<br>[0.524] | 14.12<br>[0.556] | 15.72<br>[0.619] | 13.00<br>[0.512] | 14.26<br>[0.561] | 17.04<br>[0.671] | 16.09<br>[0.633] |
| 60               | 14.50<br>[0.571] | 15.82<br>[0.623] | 16.62<br>[0.654] | 18.22<br>[0.717] | 15.50<br>[0.610] | 16.76<br>[0.660] | 19.54<br>[0.769] | 18.59<br>[0.732] |
| 80               | 19.50<br>[0.768] | 20.82<br>[0.820] | 21.62<br>[0.851] | 23.22<br>[0.914] | 20.50<br>[0.807] | 21.76<br>[0.857] | 24.54<br>[0.966] | 23.59<br>[0.929] |
| 100              | 24.50<br>[0.965] | 25.82<br>[1.017] | 26.62<br>[1.048] | 28.22<br>[1.111] | 25.50<br>[1.004] | 26.76<br>[1.054] | 29.54<br>[1.163] | 28.59<br>[1.126] |
| 120              | 29.50<br>[1.161] | 30.82<br>[1.213] | 31.62<br>[1.245] | 33.22<br>[1.308] | 30.50<br>[1.201] | 31.76<br>[1.250] | 34.54<br>[1.360] | 33.59<br>[1.322] |
| 140              | 34.50<br>[1.358] | 35.82<br>[1.410] | 36.62<br>[1.442] | 38.22<br>[1.505] | 35.50<br>[1.398] | 36.76<br>[1.447] | 39.54<br>[1.557] | 38.59<br>[1.519] |
| 160              | 39.50<br>[1.555] | 40.82<br>[1.607] | 41.62<br>[1.639] | 43.22<br>[1.702] | 40.50<br>[1.594] | 41.76<br>[1.644] | 44.54<br>[1.754] | 43.59<br>[1.716] |

X-X' Cross Section



Printed Circuit Board Layout  
(Component Side View)



TS-1149-02  
Sheet 4 of 5



Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call


800-225-5373

# 3M™ Pak 5 Socket

0.5 mm Straight Stacking, Surface Mount

PK5 Series

## STACKED MATING COMBINATIONS



## Ordering Information

### PK5 - XXXS - X - X - X - X - GGF

Contact Quantity See Table

C = With Retention Clips (Tape and Reel only)  
Omit = Without Clips

L = With Location Posts  
Omit = Without Posts

T = Tape and Reel  
Omit = In Tube

2 = Mating Height of 4 and 6 mm  
3 = Mating Height of 5 and 7 mm  
4 = Mating Height of 6 and 8 mm

TS-1149-02  
Sheet 5 of 5

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



#### 3M Electronics

6801 River Place Blvd.  
Austin, TX 78726-9000  
800/225-5373  
[www.3M.com/electronics](http://www.3M.com/electronics)

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Minimum 10%  
Post-Consumer Fiber

Printed in USA.

© 3M 2006