








LOC		DIST		REVISIONS				
ES	00	P	LYR	DESCRIPTION	DATE	OWN	APVD	
		G1		REVISED PER ECO-11-005027	14MAR2011	RK	HMR	



- PART COMPATABLE WITH XFP MSA. REFER TO THE SFP MSA FOR DIMENSIONS NOT SHOWN ON THIS PRINT.
- HOUSING: HIGH TEMPERATURE LCP, UL 94V-0 RATED, BLACK. CONTACT: PHOSPHOR BRONZE.
- CONTACTS: 0.00038 MIN GOLD IN CONTACT AREA, 0.00013 MIN GOLD ON SOLDER AREA, OVER 0.0038 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- PACKAGED PIECES PER REEL.
- GROUND, POWER AND SIGNAL PAD ARRANGEMENT TO BE DETERMINED BY CUSTOMER.
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- CONTACTS: 0.00076 MIN GOLD IN CONTACT AREA, 0.00013 MIN GOLD ON SOLDER AREA, OVER 0.0038 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- SOLDER MASK KEEP OUT AREA.
- CONTACTS: 0.00127 MIN GOLD IN CONTACT AREA, 0.00013 MIN GOLD ON SOLDER AREA, OVER 0.0038 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.



9	788862-3
7	788862-2
3	788862-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN	J. GERACE	15JAN02	TE Connectivity			
DIMENSIONS:		CHK	J. KOPPENHEFFER	15JAN02				
mm		APVD	M. WALMSLEY	15JAN02	NAME			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		PT CONNECTOR ASSEMBLY, 30 POSITION, XFP, RTANG, 0.8MM PITCH		
		9 PLC ±		108-1949		SIZE		
		3 PLC ±0.10		APPLICATION SPEC		CAGE CODE		
		5 PLC ±		114-13017		DRAWING NO		
		4 PLC ±		WEIGHT		A100779C=788862		
		ANGLES ±		CUSTOMER DRAWING		RESTRICTED TO		
MATERIAL		FINISH		SCALE		8:1		
		SEE TABLE		SHEET		1 OF 2		
						REV G1		

4805 (3/11)