

## ATC 545L Series UBC™ Ultra-Broadband Capacitor


### Features:

- EIA 0402 Case Size
- Capacitance: 100 nF
- Operating Frequency:  
16 KHz (-3 dB roll-off) to 40+ GHz\*
- Insertion Loss: < 0.5 dB typical
- Orientation Insensitive
- One Piece Construction
- Voltage Ratings: 10 and 16 WVDC
- TCC:  $\pm 15\%$  (-55°C to +125°C)
- RoHS Compliant Terminations
- Gold Terminations Available

ATC's new 545L Series Ultra-Broadband Capacitor (UBC™) is a unique component that provides ultra-low insertion loss, flat frequency response and an excellent match over multiple octaves of frequency spectrum in a one piece configuration.

The 545L is ideal for ultra-broadband DC blocking, coupling, bypassing, and feedback applications in optical communications systems and equipment using high-speed digital logic.

\*25 °C, no bias applied




*New, Patented Design*


### Advantages:

- Ultra-Broadband Performance
- Ultra-Low Insertion Loss
- Flat Frequency Response
- Excellent Return Loss
- Unit-to-Unit Performance Repeatability
- Rugged X7R Ceramic Construction

**ATC 545L Series  
Insertion Loss (S21)**



**ATC 545L Series  
Return Loss (S11)**



ATC 545L Data Sheet Test Condition Description

All testing performed on 10-mil-thick Rogers RO4350 microstrip board, with the device under test subtending a 24 mil gap in a 22-mil-wide center trace (nominal 50-ohm characteristic impedance).



AMERICAN TECHNICAL CERAMICS

ATC North America  
631-622-4700  
sales@atceramics.com

ATC Europe  
+46 8 6800410  
sales@atceramics-europe.com

ATC Asia  
+86-755-2386-8759  
sales@atceramics-asia.com




[www.atceramics.com](http://www.atceramics.com)

ATC # 001-1018  
Rev. I; 1/09


## Electrical Specifications:

- Capacitance: 100 nF
- Rated Voltages: 10 and 16 WVDC
- Dielectric Withstanding Voltage (DWV):  
250% of rated WVDC for 5 secs.
- Operating Temperature Range: -55°C to +125°C
- Temperature Coefficient of Capacitance (TCC):  
±15% (-55°C to +125°C)
- Maximum DF: 5% @ 1KHz
- Insulation Resistance:  
10<sup>8</sup> Ω min. @ +25°C @ rated WVDC  
10<sup>7</sup> Ω min. @ +125°C @ rated WVDC

## Mechanical Dimensions



## ATC PART NUMBER CODE



The above part number refers to a 545 Series (case size L) 100 nF capacitor, K tolerance (±10%), with T termination (Tin Plated over Nickel Barrier), 16 WVDC, tape and reel packaging.

ATC accepts orders for our parts using designations **with** or **without** the "ATC" prefix. Both methods of defining the part number are equivalent, i.e., part numbers referenced with the "ATC" prefix are interchangeable to parts referenced without the "ATC" prefix. Customers are free to use either in specifying or procuring parts from American Technical Ceramics.

For additional information and catalogs contact your ATC representative or call direct at (631) 622-4700.

Consult factory for additional performance data.

*Sales of ATC products are subject to the terms and conditions contained in American Technical Ceramics Corp. Terms and Conditions of Sale (ATC document #001-992 Rev. B 12/05). Copies of these terms and conditions will be provided upon request. They may also be viewed on ATC's website at [www.atceramics.com/productfinder/default.asp](http://www.atceramics.com/productfinder/default.asp). Click on the link for Terms and Conditions of Sale.*

*ATC has made every effort to have this information as accurate as possible. However, no responsibility is assumed by ATC for its use, nor for any infringements of rights of third parties which may result from its use. ATC reserves the right to revise the content or modify its product line without prior notice.*

© 2007 American Technical Ceramics Corp. All Rights Reserved.

ATC # 001-1018 Rev. I; 1/09



AMERICAN TECHNICAL CERAMICS

ATC North America  
631-622-4700  
sales@atceramics.com

ATC Europe  
+46 8 6800410  
sales@atceramics-europe.com

ATC Asia  
+86-755-2386-8759  
sales@atceramics-asia.com



[www.atceramics.com](http://www.atceramics.com)