

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION, 19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AJ	16				M	REV PER 0U20-0163-99	08NOV99	M0

- 1 MATERIALS:
INNER FERRULE: BRASS PER MIL-C-50
OUTER FERRULE: COPPER PER QQ-C-576
MOLDING: NYLON (COLOR: VIOLET)
- 2 FINISH:
INNER FERRULE: TIN PL PER MIL-T-10727
OUTER FERRULE: TIN PL PER MIL-T-10727
3. 0.84-1.50[.033-.059] PRIMARY INSULATION DIA RANGE



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± .20[.008] 3 PLC DEC ± - ANGLES ± -		DR 01/13/93 J.DAVIS		AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK 02/05/93 G.MICHAEL			
		APPD 02/05/93 G.MICHAEL		NAME CONN, COAX, R.F., TERMASHIELD, FERRULE	
		APPD 02/05/93 J.DAVIS			
MATERIAL 1		PRODUCT SPEC -		SIZE	CAGE CODE
FINISH 2		APPLICATION SPEC -		B	00779
		WEIGHT .024 OZ		SCALE	DRAWING NO C-329331
				NTS	SHEET 1 OF 1