


- VDC: 12, 24
- RPM: 1800~5200
- CFM: 4.54~16.60
- Impeller: 11 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 24; UL 1007 lead wires
- Mass:39.5g




DC FAN

60x60x15mm


Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
B6015B12L	●	12	0.10	3300	1.20	10.03	2.36	30.1	39.5
B6015S12L	○	12	0.10	3300	1.20	10.03	2.36	30.1	39.5
B6015B12M	●	12	0.12	3900	1.44	11.93	2.98	34.3	39.5
B6015S12M	○	12	0.12	3900	1.44	11.93	2.98	34.3	39.5
B6015B12H	●	12	0.15	4500	1.80	14.29	3.96	37.9	39.5
B6015S12H	○	12	0.15	4500	1.80	14.29	3.96	37.9	39.5
B6015B24L	●	24	0.04	3300	0.96	10.03	2.36	30.1	39.5
B6015S24L	○	24	0.04	3300	0.96	10.03	2.36	30.1	39.5
B6015B24M	●	24	0.08	3900	1.92	11.93	2.98	34.3	39.5
B6015S24M	○	24	0.05	3900	1.20	11.93	2.98	34.3	39.5
C6015B12L	●	12	0.08	3300	0.96	10.03	2.36	30.1	39.5
C6015S12L	○	12	0.08	3300	0.96	10.03	2.36	30.1	39.5
C6015B12M	●	12	0.12	3900	1.44	11.93	2.98	34.3	39.5
C6015S12M	○	12	0.11	3900	1.32	11.93	2.98	34.3	39.5
C6015B24L	●	24	0.04	3300	0.96	10.03	2.36	30.1	39.5
C6015S24L	○	24	0.04	3300	0.96	10.03	2.36	30.1	39.5
C6015B24M	●	24	0.05	3900	1.20	11.93	2.98	34.3	39.5
C6015S24M	○	24	0.05	3900	1.20	11.93	2.98	34.3	39.5
D6015B12L	●	12	0.08	3300	0.96	10.03	2.36	30.1	39.5
D6015S12L	○	12	0.08	3300	0.96	10.03	2.36	30.1	39.5
D6015B12M	●	12	0.12	3900	1.44	11.93	2.98	34.3	39.5
D6015S12M	○	12	0.12	3900	1.44	11.93	2.98	34.3	39.5
D6015B24L	●	24	0.04	3300	0.96	10.03	2.36	30.1	39.5
D6015S24L	○	24	0.04	3300	0.96	10.03	2.36	30.1	39.5
D6015B24M	●	24	0.05	3900	1.20	11.93	2.98	34.3	39.5
D6015S24M	○	24	0.05	3900	1.20	11.93	2.98	34.3	39.5
F6015B12L	●	12	0.10	3300	1.20	10.03	2.36	30.1	39.5
F6015B12M	●	12	0.13	3900	1.56	11.93	2.98	34.3	39.5
F6015B12H	●	12	0.15	4500	1.80	14.29	3.96	37.9	39.5
F6015B24L	●	24	0.11	3300	2.64	10.03	2.36	30.1	39.5
F6015B24M	●	24	0.11	3900	2.64	11.93	2.98	34.3	39.5
F6015B24H	●	24	0.15	4500	3.60	14.29	3.96	37.9	39.5
T6015B12U	●	12	0.14	1800~5200	1.68	4.54~16.60	0.71~5.29	22.3~41.8	39.5

Design specifics subject to change without notice.




STATIC PRESSURE





- VDC: 12
- RPM: 3000~5000
- CFM: 13.02~22.60
- Impeller: 11 blades
- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 37g




DC FAN 60x60x15mm


Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
C6015B12LA	●	12	0.10	3000	1.20	13.02	2.23	25.9	37
C6015R12LA	○	12	0.10	3000	1.20	13.02	2.23	25.9	37
F6015B12LA	●	12	0.08	3000	0.96	13.02	2.23	25.9	37
F6015R12LA	○	12	0.08	3000	0.96	13.02	2.23	25.9	37
F6015B12MA	●	12	0.13	4000	1.56	18.14	4.11	34.1	37
F6015R12MA	○	12	0.13	4000	1.56	18.14	4.11	34.1	37
F6015B12HA	●	12	0.15	4500	1.80	21.02	5.17	36.5	37
F6015B12UB	●	12	0.22	5000	2.64	22.60	6.30	39.8	37

Design specifics subject to change without notice.




STATIC PRESSURE





- VDC: 12
- RPM: 3000~5500
- CFM: 14.20~28.18
- Impeller: 9 blades
- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 36g




DC FAN

60x60x15mm

Specification

MODEL NO	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
E6015B12HY	●	12	0.13~0.28	3000~4500	1.56~3.36	14.20~22.33	2.18 ~5.25	25.7~35.1	36
F6015B12LY	●	12	0.08	3000	0.96	14.20	2.18	25.7	36
F6015B12MY	●	12	0.13	4000	1.56	19.48	4.01	33.4	36
F6015B12HY	●	12	0.15	4500	1.80	22.33	5.25	35.1	36
F6015B12UY	●	12	0.30	5500	3.60	28.18	7.82	40.0	36

Design specifics subject to change without notice.



STATIC PRESSURE

