


D

C

B

A



CABLE SIGNAL	AMPLIMITE POSITION	AMPLIMITE POSITION	CABLE SHIELD	COAX LINE NO.
PORT 1	1	3	PORT 1	1
PORT 2	5	7	PORT 2	2
PORT 3	9	11	PORT 3	3
PORT 4	13	15	PORT 4	4
PORT 5	17	19	PORT 5	5
PORT 6	21	23	PORT 6	6
PORT 7	26	28	PORT 7	7
PORT 8	30	32	PORT 8	8
PORT 9	34	36	PORT 9	9
PORT 10	38	40	PORT 10	10
PORT 11	42	44	PORT 11	11
PORT 12	46	48	PORT 12	12

- TEXT MUST BE ORIENTED SO THAT IT IS
VISABLE WITH THE TOP OF THE CONNECTOR BEING
VIEWED FROM ABOVE (OPPOSITE SIDE OF INTERFACE)
- 6 FLAME CLASS RATING PER NEC - CMG,
TEMPERATURE RATING PER NEC - 75°C
- 7 CABLE ASSEMBLIES THAT ARE SPOOLED ARE TO BE PACKAGED, SO THAT THE
CONNECTORIZED END THAT MATES TO THE SWITCH, IS THE LAST PORTION OF
THE CABLE THAT IS WRAPPED ON THE SPOOL. WHEN THE CABLE IS TO BE DEPLOYED
IT CAN ONLY BE UNWOUND FROM THE SPOOL FROM THE CONNECTORIZED END OUT
TOWARDS THE UNTERMINATED END.
- 8 CABLE TO BE TESTED FOR INDIVIDUAL COAX SHIELD CONTINUITY TO BACKSHELL.

7	225±4 FEET	1-1979525-0
7	200±4 FEET	1979525-9
7	175±3 FEET	1979525-8
7	150±3 FEET	1979525-7
7	125±3 FEET	1979525-6
7	100±3 FEET	1979525-5
7	75±3 FEET	1979525-4
	50±2 FEET	1979525-3
	25±1 FEET	1979525-2
	10±1 FEET	1979525-1
	L	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 25/JAN/07	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK G.GUTGOLD 25/JAN/07	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.GUTGOLD 25/JAN/07	CABLE ASSY.,050 SERIES AMPLIMITE DS-3, 735c COAX	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC	RESTRICTED TO	
MATERIAL -		WEIGHT -	SIZE A1	
FINISH -		CUSTOMER DRAWING		SCALE N.T.S.