

BES M30MI-PSC15B-S04G-008


Ordering code: BES046Y

M30x65 mm
GlobalProx

DC, direct current
PNP/Normally open (NO)
Sn = 15 mm
Flush (shielded)

BALLUFF

sensors worldwide



Characteristic data

Eff. switching distance S_r	15,00 mm
Tolerance S_r	$\pm 10\%$
Assured operating distance S_a	12,20 mm
Hysteresis H max. (in % of S_r)	15 %
Repeat accur. R max. (% of S_r)	5 %
Ambient temperature	-25...70 °C
Temp. drift max. (% of S_r)	10%
Switching freq. f max.	100 Hz
Ready delay t_v max.	15 ms
Utilisation category	DC 13
Function indicator	Yes
Power-on indicator	No
Short-circuit protected	Yes
Degree of protection as per IEC 60529	IP67
Protection class	II
Protected against polarity reversal	Yes
Protected against reverse connection	Yes

Electrical data

Operating voltage	
Rated operating voltage U_e DC	24,0 V
Ripple max. (% of U_e)	15 %
Voltage drop static max.	2,5 V
Rated insulation voltage U_i	250 AC V
Effective operating current I_e	200 mA
No-load current I_o damped	10 mA

No-load current I_o undamped	5 mA
Off-state current I_r max.	10 μ A
Minimum operating current I_m	0 mA
Rated short circuit current	100 A
Output resistance R_a	33.0k + D
Load capacitance max. (at U_e)	0,5 μ F

Mechanical data

Housing material	CuZn
Surface protection	Nickel-free coating
Sensing surface material	PA 12
Tightening torque max.	70 Nm
Mounting length	50 mm
Connection type	Connector
Connector type	M12x1-S04
Shock rating	Shock, half-sinus, 30 gn, 11ms
Vibration rating	55 Hz, 1 mm ampl., 3x30 min
Degree of contamination	3

Basic data

Basic standard	IEC 60947-5-2
----------------	---------------

Remarks

The sensor is functional again after the overload has been eliminated.
Embeddable: See installation notes for inductive sensors with extended switching distance 825357.
With connector, e.g. BKS-S 20-... total length = switch length +18 mm.



Definitions see main catalog

subject to change

BES M30MI-PSC15B-S04G-008

Ordering code: BES046Y

M30x65 mm

GlobalProx

DC, direct current
PNP/Normally open (NO)

Sn = 15 mm

Flush (shielded)

BALLUFF

sensors worldwide

